

An Economical and Reliable Cartridge Heater, Used in Applications Requiring Lower Operating Temperatures and Watt Densities

LDC Series



Typical Applications

- Heat Sealing Equipment
- Laminating Equipment
- Packaging Equipment
- Labeling Machines
- Molds and Dies
- Food Processing
- Refrigeration
- Shoe Machinery
- Glue Guns
- Wax Pots
- Heating Liquids
- Heating Gases

Low-density cartridge heaters are an excellent, cost effective choice without compromising quality for Original Equipment Manufacturers (OEMs) consuming large quantities of cartridge heaters for their equipment.

Standard Specifications and Tolerances

Performance Ratings

Maximum Temperature: 650°C (1200°F)

Maximum Watt Density: 3.1 to 7.0 Watt/cm² (20 to 45 Watt/in²) depending on heater size and operating temperature

Dimensional Specifications


Nominal Diameter	3/16	1/4	3/8	1/2	5/8	3/4	7/8	15/16	1	1 1/4
Actual Diameter inch	0.185	0.247	0.372	0.496	0.621	0.745	0.870	0.933	0.995	1.250
Actual Diameter mm	4.70	6.27	9.45	12.60	15.77	18.92	22.10	23.70	25.27	31.75
Diameter Tolerance	0.051 mm (±0.002")									0.127 mm (±0.005")
Length Tolerance	1.59 mm (±1/16") up to 152 mm (6") long; 3.18 mm (±1/8") over 152 mm (6") long									
Camber Tolerance	0.254 mm (0.010") per foot of length									

Electrical Specifications

Nominal Diameter	3/16	1/4	3/8	1/2	5/8	3/4	7/8	15/16	1	1 1/4
Maximum Voltage	240	240	240	240	480**	480**	480**	480**	480**	480**
Maximum Amperage	1.5	3.5	6	8	10	15	15	15	25	30
Maximum Wattage	Contact OMEGA									
Wattage Tolerance	Plus 5%, minus 10%									
Resistance Tolerance	Plus 10%, minus 5%									

* Low density cartridge heaters are UL recognized and CSA certified in many design variations under UL File Number E65652 and CSA File Number 043099. If you require UL and/or CSA Agency Approval, please specify when ordering.

**480V when applicable. Contact OMEGA.





1" Diameter, Actual 25.27 mm (0.995")

To Order Visit omega.com/lcdc8 for Pricing and Details

Model No.		Sheath Length		Watts	Watt Density	
120V	240V	mm	inch		Watt/cm ²	Watt/in ²
LDC00373	LDC00374	76.2	3	250	4.9	32
LDC00375	LDC00376	101.6	4	300	4.2	27
LDC00377	LDC00378	127.0	5	375	4.1	27
LDC00379	LDC00380	152.4	6	500	4.5	29
LDC00381	LDC00382	203.2	8	600	3.9	25
LDC00383	LDC00384	228.6	9	700	4.1	26
LDC00385	LDC00386	254.0	10	800	4.2	27
LDC00387	LDC00388	273.1	10¾	600	2.9	19
LDC00389	LDC00390	273.1	10¾	850	4.1	26
LDC00391	LDC00392	304.8	12	1000	4.3	28
LDC00393	LDC00394	355.6	14	1100	4.0	26
LDC00395	LDC00396	457.2	18	1250	3.5	23
LDC00397	LDC00398	565.2	22¼	1000	2.3	15
LDC00399	LDC00400	584.2	23	1000	2.2	14
—	LDC00401	596.9	23½	1500	3.2	21
—	LDC00402	609.6	24	1500	3.1	20

Note: Model numbers above are for low density cartridge heaters terminated with Type F flexible leads, 254 mm (10") long.

Ordering Example: LDC00392, 1000 W, 240 Vac, cartridge heater.

Order by model number from the standard sizes and ratings list on the preceding pages. Note that model numbers shown are for heaters with Type F Termination [254 mm (10") leads].

Custom Engineered/Manufactured Heaters

Because an electric heater can be very application specific, for sizes and ratings not listed, OMEGA will design and manufacture a low-density cartridge heater to meet your requirements.

Please Specify the Following:

- Diameter
- Length
- Wattage
- Voltage
- Termination Types
- Lead Length
- Cable/Braid Length
- Special Features
- Application Type
- Operating Temperature