



HARDCASE PROFESSIONAL® Rechargeable Spotlight

HCSPR611

Serious projects demand serious lighting, look no further than the *Energizer* HARDCASE PROFESSIONAL® Spotlight. This light has been designed to withstand drop after drop, off a ladder or even a two-story building. Constructed with rugged steel and rubber materials, this light is designed to meet the most demanding jobs. With advanced LED technology, the powerful beam can span the distance of four stadium fields, while high and low mode option allows the user to maximize brightness or runtime. And with a convenient, rechargeable design, users get a great performance time and time again.




Provides
550
Lumens of
Light



Provides
Run Time of
2 hours 15
minutes.



Sustains 7
Meter
Drop Test



Illuminates
objects up
to 425m
away.



Water Resistant
IPX4 - works
after splashing
water on all
sides

DESIGN BENEFITS

- ✓ Exceptionally durable construction for the most demanding jobs
- ✓ Convenient rechargeable power supply
- ✓ High and low modes for optimized brightness and runtime control
- ✓ Shatterproof lens
- ✓ Built-in lanyard slot
- ✓ 20 Year Designed to Last based on typical consumer usage patterns

LIGHT AND POWER SOURCE

- ✓ Features LED Technology
- ✓ Packed with 6 AA NiMH rechargeable batteries
- ✓ Also operates on 6 AA replaceable alkaline or lithium batteries

ELECTRICAL CHARACTERISTICS

Electrical Characteristics Nominal Power:
Power consumption 6.0W / Batteries AA
Energizer NH15-2000 9.0V dc
LED Specifications: LED 3.0V cc / 1000 mA

CERTIFICATES AND COMPLIANCE

CE RoHS
EMC, EN62471, FCC



This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Tested according to ANSI/NEMA FL1 Standards

Results based on: *Energizer*® NH15-2000

PERFORMANCE BENEFITS

- ✓ LED technology provides a bright spot for a variety of tasks
- ✓ Powerful beam distance to see objects far away
- ✓ Water resistant for outdoor tasks
- ✓ Rechargeable power supply

SPECIFICATIONS

Weight Excluding Batteries:

555 Grams / 19.6 Ounces

Dimensions:

203mm x 89mm x 64mm / 8" x 3.5" x 2.5"

NUMBER OF OPERATING MODES: 2

Mode	Lumens (lm)	Runtime (h)	Beam Distance (m)
High	550	2h 15m	425
Low	200	6h 45m	270

Before using your flashlight, please read all instructions and cautionary marking on the package and the light.

This datasheet contains information specific to products manufactured at the time publication. Contents do not constitute a claim or warranty.

©2018 Energizer