DATA SHEET

PTCA12 FLAT FOOD THERMISTOR PROBE

FLAT FOOD TEMPERATURE PROBE

Description

This probe uses the straight handle for fine control. The probe is designed for the measurement of temperature between products. Most commonly used as part of a goods inward inspection procedure. May also be used for liquid temperature measurement.

Construction

Flattened Stainless Steel blade 5mm wide blade by 85mm Long: Stainless Steel 316 (Food Grade) 2M curly polyurethane cable to tails. This provides the user with a far more robust product than the foil type of between pack probe.

Please note that this probe <u>is not</u> supplied with a connection plug for ease of hardwiring. Our thermistor probes can be purchased with jack plug as standard, other connection plugs available if required. Jack plug order code: PTCPLUG

Sensor Features

TOTAL ENCAPSULATION TECHNIQUE FOR MAXIMUM STRENGTH AND DURABILITY.

This results in a solid handle as opposed to a hollow handle. This is particularly important as there is often damage to the handles caused by excess heat. With a hollow handle it is possible to puncture the outer plastic and damage the sensor irreparably.

WATERPROOF HANDLE

Due to the total encapsulation method used, all TME probe handles are completely waterproof.

TOUGH POLYURETHANE CABLE

- Polyurethane cables are used in place of the standard PVC for the following reasons:-
- Greater retractability
- Enhanced memory of it's curl
- Non-Toxic
- · Greater mechanical strength for durability
- 12 X 0.2mm wires used internally for greater strength.
- PTFE inner insulation for strength and retractability.

HIGH ACCURACY THERMISTOR

2k2 NTC Thermistor Sensor : $(\pm 0.2^{\circ}C \pm 0.15\%)$

POLYPROPYLENE HANDLES

Polypropylene is an extremely tough and durable material, commonly used for milk crates, it has good low temperature performance and a relatively high melt temperature. It performs exceptionally well under chemical attack.

➤ WIDE AMBIENT TEMPERATURE SPECIFICATION : -50 TO 50 °C
➤ TIME RESPONSE (96% of value in water) : 10 Secs
➤ MEASUREMENT RANGE : -50 TO 150 °C

Cross-reference for compatible instruments

Suitable instruments for use with this probe

	DESCRIPTION	APPLICATION
MM2040	THERMISTOR INSTRUMENT	HIGH ACCURACY THERMISTOR THERMOMETER