

# GSM200 Desktop Indoor Air Quality CO2 Monitor


**Simultaneously displays CO2, Temperature, Relative Humidity, Time and Date**

**Features:**

- 3 Carbon Dioxide status indicators (Good / Normal / Poor) change with CO2 concentration
- User programmable audible/visual CO2 alarms (Good (default 800ppm), Poor (default 1200ppm) with disable)
- Built-in CO2 Automatic baseline calibration for long term drift compensation
- Utilizes NDIR sensor (non-dispersive infrared) waveguide technology
- Real time calendar with date and time
- Min/Max records highest and lowest readings for CO2, Temperature and Humidity
- Data Hold freezes the reading on the display
- °F/°C selectable
- Includes AC adaptor

**Applications:**

Monitor air quality in office buildings, schools, exhibition halls, shopping malls, meeting rooms, fitness centers, restaurants and other public places.



**Specifications**

Carbon Dioxide (CO2)	0 to 9999ppm
Accuracy	±75ppm or 5% of reading
Air Temperature	23 to 122°F (-5 to 50°C)
Accuracy	±2.7°F/1.5°C
Relative Humidity	0 to 90.0%RH
Accuracy	±5%RH
3 Status Icons	Good 0 to 800ppm Normal 800 to 1200ppm Poor >1200ppm
Automatic Baseline Calibration	Every 7 days
CO2 Alarm	Audible/Visual
Power	AC Adaptor (included)
Dimensions	4.6 x 4.0 x 4.0" (117 x 102 x 102mm)
Weight	7.2oz (204g)

**Ordering Information:**

GSM200      Desktop Indoor Air Quality CO2 Monitor

