



PART NO.	MATERIAL	COLOR
PCG-1-48	NYLON 66/6 (RMS-21)	NATURAL
PCG-2-48	ABS (RMS-09)	GRAY
PCG-3-48	ABS (RMS-09)	GRAY
PCG-4-48	RIGID PVC (RMS-04)	GRAY
PCG-5-48	RIGID PVC (RMS-04)	GRAY

*PARTS AVAILABLE BY SPECIAL ORDER ONLY



*PCG-1-48




*PCG-2-48



PCG-3-48



PCG-4-48



*PCG-5-48

NOTES:

1. ALL GUIDES TO ACCEPT A NOMINAL 1/16 (1.6) THICK BOARD
2. PCG-3, -4, AND -5 AVAILABLE WITH ADHESIVE BACKING. TO ORDER ADD "A" TO PART NO. EXAMPLE: PCG-XA-48
3. TAPE: 1/16 (1.6) THICK, ACRYLIC ADHESIVE TAPE (RMS-15)
4. COLOR BLACK AVAILABLE BY SPECIAL ORDER. TO ORDER ADD "BK" TO END OF THE PART NO.

TITLE: PRINTED CARD GUIDES					DWG IN IN (MM)	
TOLERANCES UNLESS NOTED .XX=±.02 .XXX=±.015 FRAC=±1/32 ANG=±1°	FILE # PCG	DWN: JK	DT: 4.18.00	FINAL		
	MAT'L: SEE TABLE	CHKD:	ENG:	PART #		PRINT TYPE CA
	RE:	SEE TABLE				

I	SEE ECN # 1352 FOR CHANGES	SK 08.09.07
H	SEE ECN # 1153	S.J. 4.13.06
-	SEE ENGINEERING FOR REV. A THRU G	-
REV	DESCRIPTION	ENGR DATE