





TO SNAP-LOCK IN A $.157 \pm .003$
(4.0 ± 0.08) DIA. HOLE,
IN A .062 (1.57) THK. BOARD.




TO SNAP-LOCK IN A $.213 \pm .003$ (5.41 ± 0.08)
DIA. HOLE, IN A .059 TO .065 (1.50 TO 1.65)
THK. PANEL/CHASSIS.

NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01).
FLAME RETARDANT: NYLON (RMS-19).
BY SPECIAL ORDER.
2. COLOR: NATURAL.

PART NO.	DIM. "A" $\pm .015$ (0.4)
RLCBSRE-4-01	1/4 (6.4)
RLCBSRE-6-01	3/8 (9.5)
RLCBSRE-8-01	1/2 (12.7)
RLCBSRE-10-01	5/8 (15.9)

BY SPECIAL ORDER. 2. COLOR: NATURAL.			TITLE: REVERSE LOCKING CKT. BD. SUPPORT, ENGLISH						DWG IN IN(MM)			
			TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.015 FRAC=1/64 ANG=1°	FILE # RLCBSRE MAT'L: SEE NOTE RE:		DWN: P.B. DT: 05-23-95		APP: DT:		FINAL		
C	CHANGED FILE NUMBER		SM 05.03.01							PART # SEE TABLE		PRINT TYPE CA
B	MAT'L RMS-19 ADDED		J.L. 12.29.97									
A	CONVERTED TO AUTOCAD		PB 05.23.95									
REV	DESCRIPTION		ENGR DATE									

PRINT
TYPE
CA