



Terminals & Splices > Automotive Terminals > GET .64 CONNECTOR SYSTEM, RECEPT AND TAB



Terminal & Splice Type: **Receptacle**
Mating Tab Width: **1 mm [.039 in]**
Mating Tab Thickness: **.64 mm [.025 in]**
Terminal Transmits: **0 – 24 A (Low Power)**
Wire Size: **20 – 18 AWG**

[All GET .64 Connector System, Recept and Tab \(29\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Clean Body
Automotive Terminal Wire Type	Copper

Contact Features

Typical Current Rating	1 A
Crimp Type	F-Crimp
Terminal & Splice Type	Receptacle
Mating Tab Width	1 mm[.039 in]
Mating Tab Thickness	.64 mm[.025 in]
Automotive Terminal Interface Plating	Tin (Sn)
Contact Termination Area Plating Material	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Automotive Terminal Termination Method	Wire

Dimensions

--	--



Wire Size	.5 – .75 mm ²
Wire Size Search	18 AWG, 19 AWG, 20 AWG
Wire Insulation Diameter	1.6 – 1.9 mm[.055 – .081 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C, 145 °C, 150 °C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F][293 °F][302 °F]
Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]

Packaging Features

Packaging Method	Reel
Packaging Quantity	10000

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

Also in the Series | [Get .64 Connector System](#)



Automotive Connector Caps & Covers (7)



Automotive Headers(2)



Automotive Housings(121)



Automotive Terminals(29)




Insertion & Extraction Tools(1)

Customers Also Bought




TE Part #1207894011
CGAT-39/13-0-SP




TE Part #368500-1
070 MLC PLUG HSG 3P




TE Part #928966-2
SPT REC 6.3 Contact SWS Sn




TE Part #967542-2
SENS FLA-KONT 2,8



TE Part #1393364-2
V23540X7000Y 12=GET FEM TERM A



TE Part #280289-5
MODULAR RELAY CONN.



TE Part #1338692-2
ANVIL



TE Part #7-2151835-7
OCEAN_2.0_SPARE_PART_KIT-055F0700



TE Part #926982-1
CI 2 STIFT



TE Part #1745025-1
SUPERSEAL 2 POS. PLUG ASSY (CLOSED CAVIT)

Documents



Product Drawings

V23540X7000Y 22=GET-FEM TERM A

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1393365-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1393365-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1393365-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

GET 0.64 Interconnection System

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English