

# Specifications

### Voltage

- Floating outputs on spring terminal block for 2,5 mm2 (AWG12) wires
- Output voltage : adujustable from 10 to 15 V. • Regulation : <25 mV for a load variation from 0 to 100% 5 mV for a line variation from -10 to +10% : < 3 mV rms including : • Ripple 3 mV peak to peak of the signal at 65 kHz < 4 mV peak to peak of the signal at 100 Hz < 35 mV peak to peak of switching spikes • Hold-up time : 50 ms at full load (230 V line input)
- Indicator : green power-on LED indicator

#### Current

- Max I
- : 3 A at 10 V 2,5 A at 12 V 2 A at 15 V

#### Power

• Max output power : 30 W

#### **Protections**

- Against short-circuits by circuit breaker with automatic reset
- Against transients on the primary circuit by varistor
- Against overcurrent on primary circuit by fuse

## **Remote sensing**

- Correction of the voltage drop in the wires (4 wires method)
- Input on disconnect scribe terminal blocks for 2,5 mm2 wires (AWG12)
- : Max 3 V (1,5 V per wire) Correction
- : < 30 mV for a load variation from 0 to max. • Ripple


# Other specifications

- Safety : Class II, Safety Extra Low Voltage (SELV),
  - complies with EN 61010-1, EN 61010-2-201 and EN 61368-1.
- EMC : Complies with EN 61000-6-2 and EN 61000-6-4.
- Overvoltage Category : II ; Pollution Degree : 2.
- Installation altitude : < 2000 m.
- : IP30 Protection level
- Operating temperature : from -25 °C to +70 °C Derating : 1 W/°C from. +55 °C
- : 190 to 264 V, 50-60 Hz • Input voltage
- Mains input : disconnect scribe terminal blocks for 2,5 mm<sup>2</sup> wires (AWG12)
- Power consumption : max 35 W
- Dielectric strength
- : 3000 VAC from input to output • Presentation
- Dimension
- Mounting



- : Clipspackage integrated in modular case for DIN rail
  - profile 35x7,5 mm or 35x15 mm

removable wall mounting integrated case to the 4 mm screws.



55 I www.elc.fr