



- PRECISE** : Output ripple < 3 mV rms.
- COMPLIE** : EN 61000-3-2 Built in actif power corrector (PFC).
- DIAGNOSTIS** : Alarm by Relay with invert contact.
- PRACTICAL** : Output voltage adjustable from 10 to 15 V.
- UNIVERSAL** : 198 to 440 V main input voltage.
- POWERFUL** : To cumulate n+1 (Parallel active mode).
- PROTECTED** : against short circuit.
- EASY** : Direct DIN rail mounting  
- Spring terminal block.



**300 WATTS**  
12 V (Adj. 10 to 15 V)  
25 A



Specifications

**Voltage**

- Floating outputs on dual spring terminal blocks with levers for 2,5 mm<sup>2</sup> (AWG 12) wire.
- Output voltage : adjustable from 10 to 15 V.
- Regulation : < 40 mV for a load variation from 0 to 100%.  
< 5 mV for a line variation from 198 to 440 V.
- Ripple : < 3 mV rms including :  
< 8 mV peak to peak of the signal at 100 kHz  
< 5 mV peak to peak of the signal at 100 Hz  
< 40 mV peak to peak of switching spikes
- Internal resistance : < 2 mΩ
- Hold-up time : 25 ms at half load and 12 ms at full load (198 V line input).
- Indicator : green power-on LED indicator.  
overheat or overvoltage red LED indicator.
- Information Relay : Invert contact, 250 VAC (30 VDC) 1 A.

**Current**

- Max I : 25,5 A in short circuit condition.  
25 A from 10 to 12 V, 20 A 15 V

**Power**

- Max output power : 300 W from 12 to 15 V, 250 W at 10 V.

**Protections**

- Against short circuits by current limit.
- Against overcurrent on primary circuit by internal fuse.
- Against output overload by voltage limiting to 17 V.
- Against current reverse power surges on the output, by fuse.

**Other specifications**

- Safety : Complies with EN 61010-1, EN61010-2-201 and EN 62368-1.
- EMC : Complies with EN 61000-6-2 and EN 61000-6-4.
- Insulation Class : I.
- Overvoltage Category : II ; Pollution Degree : 2.
- Installation altitude : < 2000 m.
- Protection level : IP 30.
- Operating temperature: +5 to 45 °C.
- Input voltage : 220-400 VAC (198 to 440 Volts), 50-60 Hz.
- Mains input : Dual spring terminal blocks for 1,5 mm<sup>2</sup> (AWG 16) wire.
- Power consumption : 360 W max.
- Power factor : 0,99 (built with PFC).
- Dielectric strength : 4000 VAC between input and output.  
2500 VAC from input to chassis.
- Presentation : galvanized steel case and front panel with epoxy finish.
- Mounting : Integral symmetrical DIN rail clips.

**Paralleling**

- Load share controller (1 wire) on dual spring terminal blocks for 1,5 mm<sup>2</sup> wire (AWG 16).

