

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0791098404](#)  
**Status:** **Active**  
**Overview:** Milli-Grid Connector System  
**Description:** Milli-Grid Receptacle, Surface Mount, Vertical, Top/Bottom Entry, without Press-fit Plastic Pegs, with Cap, Embossed Tape on Reel, 0.38µm Gold (Au) Selective, 10 Circuits, Lead-Free

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification 503940001-AS-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-70873-0259-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-79107-001 (PDF)</a>	

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	PCB Receptacles
Series	<a href="#">79109</a>
Application	Board-to-Board, Signal
Overview	<a href="#">Milli-Grid Connector System</a>
Product Name	Milli-Grid
UPC	822348492282

**Physical**


Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	272.999/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.381µm
Plating min - Termination	1.905µm
Polarized to PCB	No
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	010
Lead-free Process Capability	REFLOW
Max. Cycles at Max. Process Temperature	001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per -  
D(2021)4569-DC (8  
July 2021)  
Dipentyl phthalate  
bis(2-(2-  
methoxyethoxy)ethyl)  
ether  
Benzo(ghi)perylene  
Octanoic acid,  
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-  
pen  
Dodecamethylcyclhexasiloxane  
Decamethylcyclpentasiloxane  
Octamethylcycltetrasiloxane  
1,2-diethoxyethane  
Dibutyltin-dichloride  
1,3-Propanesultone  
C.I. Direct Black 38  
Ammonium-  
pentadecafluorooctanoate  
2,4-Di-tert-butyl-6-(5-  
chlorobenzotriazol-2-  
yl)p  
Disodium-octaborate  
Dibutylbis(pentane-2,4-  
dionato-O,O')tin  
2-(2H-Benzotriazol-2-  
yl)-4,6-  
ditertpentylphenol  
Terphenyl,  
hydrogenated  
1,2-  
Benzenedicarboxylic  
acid, dihexyl ester,  
bra  
diisohexyl phthalate  
1,2-  
Benzenedicarboxylic  
acid, dipentyl ester, br

**China RoHS**

Process Temperature max. C

260

**Material Info**

**Reference - Drawing Numbers**

Application Specification

503940001-AS-000

Packaging Specification

PK-70873-0259-001

Product Specification

PS-79107-001

Sales Drawing

SDA-79109-XXXX-001

n-pentyl-  
isopentylphthalate  
Boric acid  
Aluminosilicate  
Refractory Ceramic  
Fibres  
Zirconia  
Aluminosilicate  
Refractory Ceramic  
Fibr  
Nonadecafluorodecanoic  
acid (PFDA) and its  
sodiu  
Tris(4-nonylphenyl,  
branched and linear)  
phosphi  
Perfluorobutane  
sulfonic acid (PFBS)  
and its sal  
Fluoranthene  
Pyrene  
Dioctyltin dilaurate,  
stannane, dioctyl-,  
bis(co  
Perfluorononan-1-  
oic acid  
(2,2,3,3,4,4,5,5,6,6,7  
Methylhexahydrophthalic  
anhydride  
reaction mass of  
2-ethylhexyl 10-  
ethyl-4,4-dioct  
Perfluorohexane-1-  
sulphonic acid and its  
salts  
Lead chromate  
Tris(2-chloroethyl)  
phosphate  
Boric acid, disodium  
salt, hydrate  
Strontium-chromate  
1,2-  
Benzenedicarboxylic  
acid, di-C7-11-  
branched  
bis(2-methoxyethyl)  
ether  
1,2-  
Benzenedicarboxylic  
acid, bis(2-  
methoxyethyl  
1,2-Dimethoxyethane  
1,2-bis(2-  
methoxyethoxy)ethane  
Decabromodiphenylether  
Cadmium-oxide  
Cadmium-sulphide  
Lead  
Cadmium  
pyrochlore, antimony  
lead yellow  
Lead-dinitrate  
Lead oxide sulfate  
(Pb2O(SO4))  
Lead-titanium-trioxide

Pentalead-tetraoxide-  
sulphate  
Trilead-dioxide-  
phosphonate  
Tetralead-trioxide-  
sulphate  
Dioxobis(stearato)trilead  
Lead titanium  
zirconium oxide  
Cyanamide, lead(2+)  
salt (1:1)  
Cadmium Hydroxide  
Sulfurous Acid, Lead  
Salt, Dibasic  
Silicic acid (H<sub>2</sub>Si<sub>2</sub>O<sub>5</sub>),  
barium salt (1:1),  
lead-  
[Phthalato(2-)]dioxotrilead  
Fatty Acids, C16-18,  
Lead Salts  
N,N-  
Dimethylformamide  
Dicyclohexyl-  
phthalate  
Dihexyl-phthalate  
Phenanthrene  
Imidazolidine-2-thione

**Halogen-Free  
Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[79109](#) Series

**Mates With**

Milli-Grid Header [87833](#) , [87832](#) , [87831](#) ,  
[87758](#) , [87759](#) , [87760](#) <br> Milli-Grid Low-  
Halogen Header [151117](#) , [151118](#) , [151119](#) ,  
[151120](#)

This document was generated on 09/13/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**