

CV dimmers with Bluetooth



Areas of application

- Suitable for indoor installations
- Shops and hospitality: retail, hotels, restaurants
- Museums, residential buildings

Product family benefits

- Control of white, Tunable White, RGB and RGBW LED modules
- Independent housing for ceiling installation
- Support of systems based on CASAMBI lighting control solutions
- Minimal installation effort
- Dry contacts for optional connection to any commercial pushbutton

Product family features

- Wireless 4-channel dimmer, with a output voltage of 12 V and 24 V
- Control of LED loads of up to 240 W
- Wireless module based on Bluetooth Low Energy

Product family datasheet

Technical data

Electrical data


Product description	Nominal input voltage
OT BLE DIM	12...24 V

Dimensions & weight

Product description	Mounting hole spacing, length	Mounting length	Product weight	Cable cross-section, input side	Cable cross-section, output side
OT BLE DIM	164.0 mm	164.0 mm	200.00 g	0.5...1.5 mm ²	0.5...1.5 mm ²

Product description	Wire preparation length, input side	Wire preparation length, output side	Width	Height	Length
OT BLE DIM	10 mm	10 mm	42.0 mm	20.0 mm	172.0 mm

Product line drawing



OT BLE DIM

Product family datasheet

Colors & materials

Product description	Casing material
OT BLE DIM	Plastic

Temperatures & operating conditions

Product description	Ambient temperature range	Maximum temperature at tc test point	Temperature range at storage	Permitted rel. humidity during operation
OT BLE DIM	-20...+45 °C	65 °C	-40...+85 °C	5...85 % ¹⁾

¹⁾ Maximum 56 days/year at 85 %

Lifespan

Product description	ECG lifetime
OT BLE DIM	50000 h ¹⁾

¹⁾ At $T_{case} = 65^{\circ}C$ at T_c point / 10% failure rate

Certificates & standards

Product description	Approval marks – approval	Standards	Type of protection
OT BLE DIM	CE	Acc. to EN 55015/Acc. to EN 61547/Acc. to EN 61347-2-11/Acc. to ETSI EN 300 328/Acc. to ETSI EN 301 489-17	IP20

Logistical data

Product description	Commodity code
OT BLE DIM	853710989900

Application advice







For more detailed application information and graphics please see product datasheet.

Sales and Technical Support

Sales and Technical Support www.osram.com

Product family datasheet

Download Data

File	
	User instruction OPTOTRONIC LED Power Supply
	User instruction OPTOTRONIC LED Power Supply
	Product Datasheet Product datasheet OT BLE DIM (EN)
	Brochures OPTOTRONIC constant-voltage LED power supplies and controls (EN)
	Brochures Light is smart color control - Intuitive light management (EN)
	Declarations of conformity EU Declaration of Conformity 3595862

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899557833	OT BLE DIM	Shipping carton box 20	351 mm x 222 mm x 68 mm	5.30 dm ³	4530.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.