

6450849-7 ✓ ACTIVE

MULTI-BEAM | MULTI-BEAM XLE

TE Internal #: 6450849-7

MULTI-BEAM XLE, Rectangular Power Connectors, Header, Plug, Board-to-Board, 40 Position, 5.08mm [.2in] Centerline, Printed Circuit Board, UL 94V-0

[View on TE.com >](#)



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Plug**

Connector System: **Board-to-Board**

Number of Positions: **40**

Centerline (Pitch): **5.08 mm [.2 in]**

Features

Product Type Features

Header Type	Fully Shrouded
Rectangular Power Connector Type	Header
Connector & Housing Type	Plug
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	40
PCB Mount Orientation	Right Angle
Number of Power Positions	8
Number of Signal Positions	32
Number of Rows	4

Electrical Characteristics

Operating Voltage	60 VDC
-------------------	--------



Contact Features

Power Contact Base Material	Tin
Contact Current Rating (Max)	50 A
Contact Retention Within Housing	Without
Contact Type	Pin
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Noble Metal
Contact Mating Area Plating Material Thickness	.76 μ m[30 μ in]
Underplate Material Thickness	5.33 μ m

Termination Features

Termination Post & Tail Length	5.33 mm[.21 in]
Termination Method to Printed Circuit Board	Through Hole - Press-Fit

Mechanical Attachment

PCB Mount Retention	With
PCB Mount Retention Type	Action/Compliant Tail
Connector Mounting Type	Board Mount
Mating Retention Type	Action/Compliant Tail

Housing Features

Centerline (Pitch)	5.08 mm[.2 in]
Housing Color	Black
Housing Material	High Temperature Thermoplastic

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-40 – 125 °C, -40 – 125 °C[-40 – 257 °F][-40 – 257 °F]
-----------------------------	--

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	High Temperature Part - Not Glow Wire

Packaging Features

Packaging Method

Tray

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUL 2021
(219)
Candidate List Declared Against: JUL 2021
(219)
Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | [MULTI-BEAM XLE](#)



Rectangular Power Connectors(108)

Customers Also Bought

TE Part #120521-1
1FHR,64,30A/P,S,N,S08,09,10TE Part #120527-1
1FHP,64,30A/P,S,N,S10,12,13,15TE Part #1-1469492-2
MULTIGIG RT 9MM GUIDE/ESD 45 DEGTE Part #1-6450869-4
V/R 2ACP+1LP+32S+3HDP+1LP+1P DEGTE Part #1-1469492-1
MULTIGIG RT 9MM GUIDE/ESD 0 DEGTE Part #1-1469492-7
MULTIGIG RT 9MM GUIDE/ESD 270 DEGTE Part #1-1469492-8
MULTIGIG RT 9MM GUIDE/ESD 315 DEGTE Part #1-1734328-2
Mini USB AB R/A,Rcpt,SMT,T&R, 0.6 mmTE Part #YDTS24W17-06SNV001
RECP ASSYTE Part #1-2000713-2
RA Keyed Guide Mod, Vita 46, Machined

Documents

Product Drawings

[MBXLE R/A HED 2ACP+1LP+32S+3HDP+1LP+1P](#)

English

CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_6450849-7_3.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_6450849-7_3.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6450849-7_3.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1](#)

English

Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English