

RUSTINS STYRENE-FREE PROFESSIONAL WOODFILLER

Page: 1

Compilation date: 03/09/2021

Revision No: 1

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: RUSTINS STYRENE-FREE PROFESSIONAL WOODFILLER

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Company name: Rustins Ltd.

Waterloo Road Cricklewood London NW2 7TX

United Kingdom

Tel: +44 (0)208 450 4666
Fax: +44 (0)208 452 2008
Email: rustins@rustins.co.uk

1.4. Emergency telephone number

Emergency tel: +44 0208 450 4666

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317

Most important adverse effects: Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation.

2.2. Label elements

Label elements:

Hazard statements: H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

Hazard pictograms: GHS07: Exclamation mark



Signal words: Warning

Precautionary statements: P261: Avoid breathing dust/fume/gas/mist/vapours/spray.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P302+P352: IF ON SKIN: Wash with plenty of water.

RUSTINS STYRENE-FREE PROFESSIONAL WOODFILLER

Page: 2

P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P321: Specific treatment (see supplemental first aid instruction on this label)

D262 LD264: Take off contaminated elething and week it hefers rough

P362+P364: Take off contaminated clothing and wash it before reuse.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

STYRENE-FREE UNSAT POLYESTER

EINECS	CAS	PBT / WEL	CLP Classification	Percent
-	-	-	Flam. Liq. 3: H226; Skin Irrit. 2: H315;	70-90%
			Eye Irrit. 2: H319; Skin Sens. 1: H317	

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash

immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a

doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may

cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used.

RUSTINS STYRENE-FREE PROFESSIONAL WOODFILLER

Page: 3

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact

with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from

downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Do not create dust.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Transfer to a closable, labelled salvage container for disposal by an appropriate

method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.

Do not handle in a confined space. Avoid the formation or spread of dust in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

RUSTINS STYRENE-FREE PROFESSIONAL WOODFILLER

Page: 4

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency. Respiratory

protective device with particle filter.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste

Colour: Various

Odour: Characteristic odour Evaporation rate: No data available.

Oxidising: No data available.

Solubility in water: Not miscible

Also soluble in: Most organic solvents.

Viscosity: Highly viscous

Boiling point/range°C: No data available. **Melting point/range°C:** No data available.

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: 52 Part.coeff. n-octanol/water: No data available.

Autoflammability°C: No data available. Vapour pressure: No data available.

Relative density: approx. 2.0 pH: Approx. 7

VOC g/I: No data available.

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

RUSTINS STYRENE-FREE PROFESSIONAL WOODFILLER

Page: 5

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	DRM	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may

cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Insoluble in water.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

RUSTINS STYRENE-FREE PROFESSIONAL WOODFILLER

Page: 6

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal

company.

NB: The user's attention is drawn to the possible existence of regional or national

regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN3269

14.2. UN proper shipping name

Shipping name: POLYESTER RESIN KIT

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

Packing group: |||

14.5. Environmental hazards

Environmentally hazardous: No Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: E
Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture

by the supplier.

Section 16: Other information

RUSTINS STYRENE-FREE PROFESSIONAL WOODFILLER

Page: 7

Other information

Other information: according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation

(EU) 2015/830

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive

and shall be used only as a guide. This company shall not be held liable for any

damage resulting from handling or from contact with the above product.