

RoHS
Compliant



Features

- Semi-rigid, adhesive lined, polyolefin tubing
- 3:1 shrink ratio
- Splash-resistant, moisture-resistant covering
- Rugged protection against abrasion, vibration and flexing
- Excellent strain relief and insulation of weak points
- Operation temperature range : -45°C to +125°C
- Minimum Shrink Temperature +70°C
- UL Approval: UL224, 125°C 600V VW-1 (except clear)

Product Properties

Technical Data Out Jacket Material

Property	Test Method	Typical Data
Tensile Strength	ASTM D 2671	≥12MPa
Ultimate Elongation	ASTM D 2671	≥300%
Longitudinal Shrinkage	UL 224	±8%
Heat Aging Ultimate Elongation	158°C, 168hrs	≥200%
Flammability	VW-1	Pass (out jacket only)
Dielectric Strength	IEC 243	≥15kV/mm
Volume Resistivity (ohm-cm)	UL224	≥10 ¹⁴ Ω.cm
Copper Stability	ASTM D 2671	Pass
Corrosion	UL224	No corrosion

Technical Data Adhesive

Property	Test Method	Typical Data
Water Absorption	ISO 62	<0.2%
Softening Point	ASTM D E28	95°C
Peel Strength (to PE)	ASTM D 1000	120N/25m
Peel Strength (to AL)	ASTM D 1000	80N/25m

Dimension Table

Size		As supplied (mm)	After Recovered (mm)		
Inch	mm	Internal Diameter Min.	Internal Diameter Max.	Total Wall Thickness	Wall Thickness of Adhesive
1/8	Ø3.2	3.6 ±0.4	1	0.9 ±0.3	0.4 ±0.2
3/16	Ø4.8	5.2 ±0.4	1.6	1.05 ±0.3	0.4 ±0.2
1/4	Ø6.4	7 ±0.5	2.2	1.25 ±0.3	0.45 ±0.2
5/16	Ø7.9	8.5 ±0.5	2.7	1.35 ±0.3	0.45 ±0.2
3/8	Ø9.5	10 ±0.5	3.2	1.45 ±0.3	0.5 ±0.2
1/2	Ø12.7	13.2 ±0.5	4.2	1.65 ±0.3	0.5 ±0.2

Heat Shrink Tubing



Size		As supplied (mm)	After Recovered (mm)		
Inch	mm	Internal Diameter Min.	Internal Diameter Max.	Total Wall Thickness	Wall Thickness of Adhesive
5/8	Ø15	15.5 ±0.5	5.2	1.8 ±0.3	0.55 ±0.3
3/4	Ø19.1	19.8 ±0.7	6.3	1.95 ±0.3	0.6 ±0.3
1	Ø25.4	25.4	8.5	2 ±0.4	0.6 ±0.3
1-1/4	Ø30	30	10.2	2.15 ±0.4	0.65 ±0.3
1-1/2	Ø39	39	13.5	2.15 ±0.4	0.65 ±0.3
2	Ø50	50	17	2.45 ±0.4	0.75 ±0.3

Part Number Table

Description	Part Number
Heat Shrink Tubing, 3:1, 3.2mm, Black, 10m	HS114
Heat Shrink Tubing, 3:1, 4.8mm, Black, 10m	HS115
Heat Shrink Tubing, 3:1, 6.4mm, Black, 10m	HS116
Heat Shrink Tubing, 3:1, 7.9mm, Black, 10m	HS117
Heat Shrink Tubing, 3:1, 9.5mm, Black, 10m	HS118
Heat Shrink Tubing, 3:1, 12.7mm, Black, 10m	HS119
Heat Shrink Tubing, 3:1, 15mm, Black, 10m	HS120
Heat Shrink Tubing, 3:1, 19.1mm, Black, 10m	HS121
Heat Shrink Tubing, 3:1, 3.2mm, Black, 1.2m	HS114 1.2M
Heat Shrink Tubing, 3:1, 4.8mm, Black, 1.2m	HS115 1.2M
Heat Shrink Tubing, 3:1, 6.4mm, Black, 1.2m	HS116 1.2M
Heat Shrink Tubing, 3:1, 7.9mm, Black, 1.2m	HS117 1.2M
Heat Shrink Tubing, 3:1, 9.5mm, Black, 1.2m	HS118 1.2M
Heat Shrink Tubing, 3:1, 12.7mm, Black, 1.2m	HS119 1.2M
Heat Shrink Tubing, 3:1, 15mm, Black, 1.2m	HS120 1.2M
Heat Shrink Tubing, 3:1, 19.1mm, Black, 1.2m	HS121 1.2M
Heat Shrink Tubing, 3:1, 25.4mm, Black, 1.2m	HS122 1.2M
Heat Shrink Tubing, 3:1, 30mm, Black, 1.2m	HS123 1.2M
Heat Shrink Tubing, 3:1, 39mm, Black, 1.2m	HS124 1.2M
Heat Shrink Tubing, 3:1, 50mm, Black, 1.2m	HS125 1.2M

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands

