# **PSI Displays Ltd**

# www.psidisplays.co.uk

Copyright @2008 by this company. No. Part of this publication may be reproduced, transmitted, transcribed, stored in a retrieval system or translated into any language or computer language, in any form or any means. Electronic, mechanical, magnetic, optical, chemical, manual or otherwise, without the prior written permission of this company.

#### SAFETY INSTRUCTION

- 1. Never push objects of any kind, or spill liquid of any kind into these products.
- 2. Do not attempt to service this product yourself, as opening or removing covers may expose you to dangerous voltage points or other risk. Refer all servicing to qualified service personnel, if any misuse mentioned above happened or any accident dropping, miss-operations occurred.

#### 7. Security notes

The unit is only suitable for indoor use. The heat being generated in the unit has to be removed via air circulation. Therefore the circulation vents at the housings must not be covered with any objects.. Do not insert or drop anything into the air vents! This could result in a short-circuit. If the unit is used for purposes other than originally intended, if it is connected in the wrong way or not repaired by authorized skilled personnel, there is no liability for possible damage. To cleaning only use a dry, soft cloth, by no means chemicals or water. If the unit is to be put out of operation definitively, bring it to a local recycling plant for disposal.

#### 8. Technical Data

LCD technology: TFT active matrix

Display size: Diagonally measured 7"

Colour system: NTSC and PAL Dual System

Sync. :.hor. 15 625 Hz, vert. 50 Hz.

Number of pixels: 800 x 480

Audio level: 1V/10k Battery Charger: 15V

Dimensions: LSM-7327 Front panel 193.8x 133.2 mm

Weight: 2 Kgs

Page 1 of 6 Page 6 of 6

#### 5. Operation

1) Switch on the device with the Main power switch (12)

2) Select the right Video input (11)

3) Adjust the Brightness control + - in order to obtain an image as clear and sharp as possible.

4) Adjust the Volume for the headphones to desired level with the volume control (Optional)

5) You may push the reverse image function button ① if the monitor is connected to a Rear View Camera.

6) Please push OSD Control Menu 7 bottom to select the Brightness, Contrast, and Display Mode that you wish to change, then use + to get desired picture.

#### **Display modes:**

**a**. 4:3, **b**. Linear 16:9 **c**. Non-Linear 16:9, please use  $\boxed{+}$  bottom to change the Display modes.

**CAUTION:** When using headphones do not adjust a high vol.

Permanent high volumes may damage person's hearing! The human ear gets accustomed to high volumes which do not seem to be that high after some time. Therefore, do not further increase a high volume after getting used to it.

## 6. Application range

The LCD colour monitors offer a sharp and high contrast display. They can be universally applied, e.g. in surveillance systems, in reverse monitoring car systems or for multimedia applications. Moreover, an additional Audio input enables sound transmission via headphone

Page 5 of 6

#### 1.Contents:

1. 7" Monitor x 1 2. Carry Bag x 1

3. Waist Belt x 1 4. RCA to BNC Adapter x 4

5. 30 cm Power Lead x 1

6. 1300mA Energy Saving Li-ion Rechargeable Battery

7. 15V Battery Charger x 1, this is used only to recharge the battery.

WARNING: Do not use to power the LCD Monitor directly.




Fig. 1. Accessories

### 2. Power Operating Elements (Charging and Using Battery)

- 1. To charge the battery simply push the on-off switch to the "on" position and let the Li-ion battery charge for 8~10 hours the first time being used. Once it is fully charged or after using it, please make sure to push the switch to the "off" position in order to avoid any power drain.
- 2. Please note the red LED light is the input power indicator which informs you power from the charger is on, it does not connect to battery "In" and "Out". Note that when the red light is on, this doesn't mean the battery is charging. You will still have to push the switch "on" in order to charge or use
- 3. Please stick two velco's on the back of monitor. And Put in the proper position in the carry bag, so that the velco will be securely fastened onto the monitor to avoid vibration.
- 4. Connect the battery to monitor as power source by 30cm power cord.



Fig. 2 Energy Saving Li-ion Rechargeable Battery

#### 3. Connection

- 1) Connect the Video source to Video input I or II ((1) or (2)).
- 2) Connect the Audio input (4) (Optional)
- 3) Selector the correct Input (11) Source
- 4) Connect an electronically regulated 12V power supply (6) The positive pole must be connected to the medium contact.
- 5) Connect the Audio Out Put (5) (Optional)

### Page 3 of 6

#### 4. Connections and Controls




Fig. 3 Connectors and Controls

- Video II Input Video I Input Video Out-Put Audio Input (Optional) Audio Out-Put ((Optional) (6) DC 12V Power Input Increase (default to Brightness) OSD Menu Decrease (default to Brightness) (10) Left-Right-Up-Down Reverse (11) Video Input selector
- (12) Main Power (13) LED Power Indicator
- (14) VGA Connector on the rear side

# **PSI Displays Ltd**

www.psidisplays.co.uk

# LSM7327

7" Color Service Monitor

User's Manual

Version 3.1



