

92A - Metric angled box wrenches




Standards:

NF ISO 2236, NF ISO 691, ISO 2236, ISO 691, DIN ISO 691

Description:

- Angled box wrenches: allows to work on long threaded rods.
- Passage hole allowing to use shanks: 160A.
- Shank to use: 160A.1 for the dimensions 4 to 23 mm; 160A.2 for the dimensions 24 to 32 mm.
- Metric sizes: 4 to 32 mm.
- Presentation: satin chrome finish.

	A [mm]	Length L [mm]	Length L1 [mm]	Head Width B [mm]	Height H [mm]	Weight [Kg]
92A.10	10	118.0	36.5	16.0	23.0	0.065
92A.10PB	10	118.0	36.5	16.0	23.0	0.065
92A.11	11	118.0	36.5	17.0	23.0	0.07
92A.11PB	11	118.0	36.5	17.0	23.0	0.07
92A.12	12	127.0	43.0	19.0	27.0	0.1
92A.12PB	12	127.0	43.0	19.0	27.0	0.1
92A.13	13	127.0	43.0	20.5	27.0	0.11
92A.13PB	13	127.0	43.0	20.5	27.0	0.11
92A.14	14	136.0	49.0	21.5	31.0	0.155
92A.14PB	14	136.0	49.0	21.5	31.0	0.155
92A.15	15	136.0	49.0	22.5	31.0	0.16
92A.15PB	15	136.0	49.0	22.5	31.0	0.16
92A.16	16	145.0	55.0	24.0	35.0	0.19
92A.16PB	16	145.0	55.0	24.0	35.0	0.19
92A.17	17	145.0	55.0	26.0	35.0	0.2
92A.17PB	17	145.0	55.0	26.0	35.0	0.2
92A.18	18	154.0	61.0	27.5	39.0	0.225
92A.18PB	18	154.0	61.0	27.5	39.0	0.225
92A.19	19	154.0	61.0	28.5	39.0	0.23
92A.19PB	19	154.0	61.0	28.5	39.0	0.23
92A.20PB	20	163.0	66.5	29.5	41.5	0.32
92A.21	21	163.0	67.5	31.0	42.5	0.325
92A.21PB	21	163.0	67.5	31.0	42.5	0.325
92A.22	22	172.0	68.0	32.0	42.5	0.35
92A.22PB	22	172.0	68.0	32.0	42.5	0.35
92A.23	23	165.0	72.5	33.0	46.5	0.39
92A.24	24	175.0	74.5	34.5	45.5	0.415

92A.24PB	24	175.0	74.5	34.5	45.5	0.415
92A.30	30	195.0	86.5	42.5	53.5	0.64
92A.4	4	95.0	23.5	8.5	16.5	0.02
92A.4PB	4	95.0	23.5	8.5	16.5	0.02
92A.5	5	95.0	23.5	9.5	16.0	0.02
92A.5.5	5.5	95.0	25.0	10.0	17.5	0.025
92A.5.5PB	5.5	95.0	25.0	10.0	17.5	0.025
92A.5PB	5	95.0	23.5	9.5	16.0	0.02
92A.6	6	100.0	26.5	10.5	17.5	0.03
92A.6PB	6	100.0	26.5	10.5	17.5	0.03
92A.7	7	100.0	28.5	11.5	19.5	0.03
92A.7PB	7	100.0	28.5	11.5	19.5	0.03
92A.8	8	109.0	31.5	13.0	20.5	0.045
92A.8PB	8	109.0	31.5	13.0	20.5	0.045
92A.9	9	109.0	33.0	14.5	22.0	0.05
92A.9PB	9	109.0	33.0	14.5	22.0	0.05