

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

DEGREASER

Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Heavy duty

1.3. Details of the supplier of the safety data sheet

Premier Farnell

150 Armley Road

Leeds LS12 2QQ

Tel. : +44 (0) 8701 202530

1.4. Emergency telephone number

+44 1865 407333

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical : Aerosols, category 1
Extremely flammable aerosol.
Pressurised container: May burst if heated.

Classification is based on test data.

Health : Skin irritation, category 2
Causes skin irritation.
Specific target organ toxicity - single exposure, category 3
May cause drowsiness or dizziness.

Classification based on calculation method.

Environment : Hazardous to the aquatic environment, chronic category 2
Toxic to aquatic life with long lasting effects.

Classification based on calculation method.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier : Contains:
Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, < 5% n-hexane

Hazard pictogram(s) :   

Signal word : Danger

Hazard statement(s) : H222 : Extremely flammable aerosol.
H229 : Pressurised container: May burst if heated.
H315 : Causes skin irritation.
H336 : May cause drowsiness or dizziness.
H411 : Toxic to aquatic life with long lasting effects.
Precautionary statement(s) : P102 : Keep out of reach of children.
P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211 : Do not spray on an open flame or other ignition source.

P251 : Do not pierce or burn, even after use.
P261 : Avoid breathing dust/fume/gas/mist/vapours/spray.
P271 : Use only outdoors or in a well-ventilated area.
P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
P501-2 : Dispose of contents/container to an authorised waste collection point.
Supplemental Hazard information : Repeated exposure may cause skin dryness or cracking.

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard Statement	Notes
Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, < 5% n-hexane	01-2119475514-35	-	921-024-6	60-100	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H225, H315, H336, H304, H336, H304,	B, Q
Hydrocarbons, C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	01-2119485926-20	68512-91-4	270-990-9	10-30	Press. Gas, Flam. Gas 1	H280, H220	K, G
n-hexane	01-2119480412-44	110-54-3	203-777-6	<5	Flam. Liq. 2, Repr. 2, Asp. Tox. 1, STOT RE 2, Skin Irrit. 2, STOT SE 3, Aquatic Chronic 2	H225, H361f, H304, H373, H315, H336, H411	A
Explanation notes							
A : substance with Community workplace exposure limit							
B : substance with national established workplace exposure limit							
G : exempted from the obligation to register in accordance with art.2(7) of REACH Regulation No 1907/2006							
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)							
Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.							

(*Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes : If substance has got into eyes, immediately wash out with plenty of water
If eye irritation persists: Get medical advice/attention.
Contact with skin : Take off contaminated clothing and wash before reuse.
IF ON SKIN: Wash with plenty of soap and water.
If skin irritation occurs: Get medical advice/attention.
Inhalation : IF INHALED: Remove person to fresh air and keep comfortable for breathing.
Call a POISON CENTRE or doctor/physician if you feel unwell.

Ingestion : If swallowed do not induce vomiting because of risk of aspiration into the lungs.
If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation : Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion : After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact : May cause irritation.
Symptoms : redness and pain
Eye contact : May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice : If you feel unwell, seek medical advice (show the label where possible)
If symptoms persist always call a doctor

SECTION 5: Fire fighting measures

5.1. Extinguishing media

Foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO, CO₂

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources; Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition; Take precautionary measures against static discharges
Equipment should be earthed; Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation; Avoid contact with skin and eyes. Wash thoroughly after use.
Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Heavy duty

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
n-hexane	110-54-3	TWA	20 ppm
National established exposure limits, United Kingdom			
n-hexane	110-54-3	TWA	20 ppm

8.2. Exposure controls

Control procedures	: Ensure adequate ventilation; Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection	: Take precautions to avoid contact with skin and eyes when handling the product. In all cases handle and use the product in accordance with good industrial hygiene practices. Ensure adequate ventilation
Inhalation	: In case of insufficient ventilation, wear suitable respiratory equipment.
Recommended respiratory protection	: Air purifying respirator equipped with organic gas/vapor cartridge (type A)
Hands and Skin	: When handling the product wear chemical-resistant gloves (standard EN 374). Use a reusable glove with a minimum breakthrough time of 30 minutes. The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves	: Nitrile
Eyes	: Wear safety eyewear according to EN 166.
Environmental protection	: Avoid release to the environment. Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Appearance : physical state	: Propane/butane propelled liquid.
Colour	: Colourless.
Odour	: Characteristic odor
pH	: Not applicable.
Boiling point/range	: 88-105°C
Flash point	: -12°C
Evaporation rate	: 4.2 (n-butyl acetate=1)
Explosion limits : upper limit	: 8%
Lower limit	: 1%
Vapour pressure	: Not available.
Relative density	: 0.715 g/cm ³

Solubility in water : Immiscible with water
Auto-ignition : 367°C
Viscosity : 0.61 mm²/s

9.2. Other information

NA

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO, CO₂

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity : Based on available data the classification criteria are not met
Skin corrosion/irritation : Causes skin irritation.
Serious eye damage/irritation : Based on available data the classification criteria are not met
Respiratory or skin sensitisation : Based on available data the classification criteria are not met
Germ cell mutagenicity : Based on available data the classification criteria are not met
Carcinogenicity : Based on available data the classification criteria are not met
Toxicity for reproduction : Based on available data the classification criteria are not met
STOT-single exposure : May cause drowsiness or dizziness.
STOT repeated exposure : based on available data the classification criteria are not met
Aspiration hazard : based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion : After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact : Irritating to skin.
Eye contact : May cause irritation.

Toxicological data:

Hazardous ingredient	CAS-nr.	method	
Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, < 5% n-hexane	-	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 25000 mg/m ³
		LD50 derm.rabit	> 2000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 2

Toxic to aquatic life with long lasting effects.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
Naphtha (petroleum), hydrotreated light	-	LC50 fish	> 10 mg/l
		EC50 daphnia	3 mg/l

12.2. Persistence and degradability

No information available

12.3. Bioaccumulative potential

No information available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name : AEROSOLS (hydrocarbons)

14.3. Transport hazard class(es)

Class : 2.1

ADR/RID - Classification code : 5F

14.4. Packing group

Packing group : Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous : Yes

IMDG - Marine pollutant : Marine pollutant

IATA/ICAO - Environmentally hazardous : Yes

14.6. Special precautions for user

ADR/RID - Tunnelcode : (D)
IMDG - Ems : F-D, S-U
IATA/ICAO - PAX : 203
IATA/ICAO - CAO : 203

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.

Regulation (EC) No 1907/2006 (REACH)

Regulation (EC) No 1272/2008 (CLP)

Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements : H220 : Extremely flammable gas.
H225 : Highly flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H304 : May be fatal if swallowed and enters airways.
H315 : Causes skin irritation.
H336 : May cause drowsiness or dizziness.
H361f : H361f
H373 : May cause damage to organs through prolonged or repeated exposure .
H411 : Toxic to aquatic life with long lasting effects.

Acronyms and synonyms : TWA = time weight average
STEL = short time exposure limit
VOC = volatile organic compounds
PBT = persistent bioaccumulative toxic
vPvB = very persistent very bioaccumulative.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation. The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Part Number

PPC107

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.