

192A.16VE | 192A.VE - 1,000 Volt insulated high-performance diagonal cutters



Description:

- For your safety, all pliers are tested individually at 10,000 volts for 10 seconds, at the end of the manufacturing cycle.
- New head design to increase durability and cutting capacity
- Cutting edges designed to cleanly cut all types of wire: soft wires and modern materials to a maximum piano wire specification of: - 192A.16VE : 2.0mm 210 kg/mm² - 192A.18VE : 2.2mm 205 kg/mm²
- High mechanical advantage due to off-set rivet and cutting edge geometry reducing effort.
- High durability carbon alloy steel, with induction hardened cutting edges.
- Bi-Material ergonomic grips resistant to chemical agents. - Return spring. - Tether ready (Tether point adds 10mm to nominal length).
- Varnish finish to help prevent rusting.

	192A.16VE
Diameter D Maxi [mm]	2.0
Length L [mm]	160.0

Thickness E [mm]	10.0
Head Height C [mm]	18.0
Head Width B [mm]	24.0