




GNSS

TE Internal #: 2108824-1

GNSS, Antenna, GNSS, Printed Circuit Board, Surface Mount (SMT), GNSS – Global – 1559 – 1610 MHz, Embedded, Length .394 in [10 mm]

[View on TE.com >](#)

Antennas



Wireless Application: **GNSS**

Mounts To: **Printed Circuit Board**

Antenna Connection Type: **Surface Mount (SMT)**

Application by Region: **GNSS – Global – 1559 – 1610 MHz**

Antenna Style: **Embedded**

Features

Product Type Features

Antenna Connection Type	Surface Mount (SMT)
-------------------------	---------------------

Configuration Features

Band Type	Single Band
Antenna Protocol	GNSS
Number of Ports	1
Antenna Style	Embedded

Electrical Characteristics

VSWR (Max)	<1.7:1
Impedance	50 Ω
Active Antenna	No

Signal Characteristics

Frequency Band	1559 – 1610 MHz
Gain (Max)	2.9 dB



Body Features

Product Weight	.11 g[.00388 oz]
----------------	------------------

Mechanical Attachment

Region	Global
Polarization	Linear
Mounts To	Printed Circuit Board

Dimensions

Product Length	10 mm[.394 in]
Product Width	3 mm[.119 in]
Product Height	1.5 mm[.06 in]

Usage Conditions

Application by Region	GNSS – Global – 1559 – 1610 MHz
-----------------------	---------------------------------

Operation/Application

Wireless Standard	L1/GPS Glonass Galileo
-------------------	------------------------

Industry Standards

Wireless Application	GNSS
----------------------	------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Other

Precision Level	Standard
-----------------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2118706-2
1 PC STD SHIELD, CRS-13.66X12.70X2.54MM



TE Part # 2118709-4
1 PC STD SHIELD, AL-32.00X32.00X6.00MM

Also in the Series | GNSS



Antennas(23)

Customers Also Bought



TE Part #878513-000
Bulbous Heat Shrink Boots: Lipped, Right Angle



TE Part #154717-6
PL 250 REC TERMINAL 14-11 AWG PTPB



TE Part #1-1703543-0
2POS,TAB 2.8X0.8,TAB HSG,ASSY



Documents

Product Drawings

[Chip ant., SMD, L1+G1](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2108824-1_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2108824-1_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2108824-1_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Chip ant., SMD, L1+G1](#)

English