

# KERN CKE36K0.1



Easy to use, self-explanatory counting scale with laboratory accuracy, counting resolution up to 360,000 points - now also with KERN KCP and stronger battery operation



## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

## Power supply

Battery:	6x1.5 V AAA
Charging time:	10 h
Input voltage:	110 V - 240 V AC
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK US
Operating time:	80 h
Operating time (Backlight off):	90 h
Operating time (Backlight on):	40 h
Rechargeable battery:	Rchrg. battery optional - intern

## Measuring system

Adjustment options:	External calibration
Linearity:	300 mg
Readability [d]:	100 mg
Recommended adjusting weight:	36 kg (E2)
Repeatability:	100 mg
Resolution:	360000
Stabilisation time under laboratory conditions:	3 s
Tare range:	36 kg
Warm up time:	2 h
Weighing capacity [Max]:	36 kg
Weighing system:	Strain gauge
Weighing units:	g lb dwt custom factor oz gn kg PCS ozt

## Display

Display digit height (large):	2,500 cm
-------------------------------	----------

## Counting

Counting resolution:	360000
Minimum piece weight at piece counting (Laboratory):	100 mg
Minimum piece weight at piece counting (Normal):	1 g
Reference weight:	yes

## Functions

Counting function:	yes
PRE-TARE function:	yes
Weighing with tolerance range:	yes

## Services (optional)

DAkkS Certificate:	963-128
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Counting scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	470 x 470 x 190 mm
Gross weight:	7,600 kg
Net weight:	6,500 kg
Shipping method:	Parcel service

## Construction

Dimensions housing (WxDxH):	350 x 390 x 120 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	340 x 240 mm


# KERN CKE36K0.1



Easy to use, self-explanatory counting scale with laboratory accuracy, counting resolution up to 360,000 points - now also with KERN KCP and stronger battery operation

## Piktogramme

### STANDARD



### OPTION



### FACTORY

