

## Product Information

### Double-sided tape with fabric backing

tesa® 4964 consists of a tear resistant flexible fabric backing with a rubber adhesive system.

The adhesive has a high coating weight making it well suited for mounting applications on irregular surfaces.

tesa® 4964 can be removed in most cases without leaving adhesive residues from sound surfaces.

Initial tests should be carried out before mounting tesa® 4964 on plasticised surfaces

### Main Application

- Carpet laying
- Honeycomb milling
- Laminating of shoe insoles and heel protectors (leather manufacturing)
- Splicing of fabric webs

### Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

#### Technical Data

• Backing material	cloth	• Type of adhesive	natural rubber
• Color	white	• Elongation at break	10 %
• Total thickness	390 µm	• Tensile strength	80 N/cm

#### Adhesion to

• Steel (initial)	7.5 N/cm	• Steel (after 14 days)	7.6 N/cm
• ABS (initial)	7.3 N/cm	• ABS (after 14 days)	7.8 N/cm
• Aluminium (initial)	7.2 N/cm	• Aluminium (after 14 days)	7.3 N/cm
• PC (initial)	7.4 N/cm	• PC (after 14 days)	7.5 N/cm
• PE (initial)	5.3 N/cm	• PE (after 14 days)	5.4 N/cm
• PET (initial)	6.5 N/cm	• PET (after 14 days)	7.2 N/cm
• PP (initial)	6.8 N/cm	• PP (after 14 days)	6.9 N/cm
• PS (initial)	7.2 N/cm	• PS (after 14 days)	7.5 N/cm
• PVC (initial)	6.9 N/cm	• PVC (after 14 days)	7.0 N/cm

#### Properties

• Tack	●●●●	• Softener resistance	●●●
• Ageing resistance (UV)	●●	• Static shear resistance at 23°C	●●
• Humidity resistance	●●	• Static shear resistance at 40°C	●
• Resistance to chemicals	●		

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

#### Additional Information

Additional product versions specially designed for the honeycomb milling application:

PV15: Double sided tape with fabric backing; brown glassine paper liner

# tesa® 4964

## Product Information



### Additional Information

Liner variants:

PV0: Brown glassine paper (standard)

### Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit  
<http://l.tesa.com/?ip=04964>