

## Product Information

Transparent double-sided filmic tape

tesa® 51970 is a transparent double-sided tape consisting of a PP-film backing and a tackified adhesive.

tesa® 51970 features especially:

- Excellent combination of high tack and adhesion
- Secure bond even on critical materials such as PP and PE and rough surfaces
- Good temperature resistance and outdoor suitability

## Main Application

- Mounting of plastic and wooden trims
- Mounting of decorative materials and displays
- Mounting of transparent signs and scales

## Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

### Technical Data

• Backing material	PP film	• Tensile strength	50 N/cm
• Color	transparent	• Type of liner	glassine
• Total thickness	220 µm	• Color of liner	brown
• Type of adhesive	tackified acrylic	• Thickness of liner	71 µm
• Elongation at break	150 %		

### Adhesion to

• Steel (initial)	13.0 N/cm	• Steel (after 14 days)	13.5 N/cm
• ABS (initial)	11.3 N/cm	• ABS (after 14 days)	14.4 N/cm
• Aluminium (initial)	10.2 N/cm	• Aluminium (after 14 days)	12.8 N/cm
• PC (initial)	12.3 N/cm	• PC (after 14 days)	15.0 N/cm
• PE (initial)	5.4 N/cm	• PE (after 14 days)	6.8 N/cm
• PET (initial)	9.9 N/cm	• PET (after 14 days)	12.5 N/cm
• PP (initial)	6.8 N/cm	• PP (after 14 days)	8.8 N/cm
• PS (initial)	11.8 N/cm	• PS (after 14 days)	13.4 N/cm
• PVC (initial)	10.5 N/cm	• PVC (after 14 days)	17.0 N/cm

### Properties

• Temperature resistance short term	130 °C	• Resistance to chemicals	●●●●
• Temperature resistance long term	80 °C	• Softener resistance	●●●●
• Tack	●●●●	• Static shear resistance at 23°C	●●●●
• Ageing resistance (UV)	●●●●	• Static shear resistance at 40°C	●●●●
• Humidity resistance	●●●●		

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

### Additional Information

Liner variants:

For latest information on this product please visit  
<http://l.tesa.com/?ip=51970>

# tesa® 51970

## Product Information



### Additional Information

PV0 brown glassine paper (69 µm; 80g/m<sup>2</sup>)

PV1 white paper liner (84 µm; 102g/m<sup>2</sup>)

PV2 brown glassine paper (78µm; 90g/m<sup>2</sup>)

PV6 red MOPP-film (80 µm; 72g/m<sup>2</sup>)

PV8 white MOPP friction liner (69 µm; 80g/m<sup>2</sup>)

A fingerlift version (extended liner), tesa® 61970, is also available.

According to VDA278 analysis, tesa 51970 does not contain any single substances restricted by the drafted GB regulations (China) as well as the indoor concentration guideline by Health, Labour and Welfare Ministry (Japan).

## Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit  
<http://l.tesa.com/?ip=51970>