

MAS DC/DC SELECT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Only remaining stock
available****General ordering data**

Version	MICROSERIES, Signal converter/insulator
Order No.	8594810000
Type	MAS DC/DC SELECT
GTIN (EAN)	4032248252442
Qty.	1 pc(s).

MAS DC/DC SELECT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	97.8 mm	Depth (inches)	3.85 inch
Width	6.1 mm	Width (inches)	0.24 inch
Length	88 mm	Length (inches)	3.465 inch
Net weight	51 g		

Temperatures

Storage temperature	-20 °C...85 °C	Operating temperature	0 °C...55 °C
---------------------	----------------	-----------------------	--------------

Probability of failure

MTTF	440 Years
------	-----------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Input

Input current	0...20 mA, 4...20 mA	Input resistance, current	≤ 5 Ω
Input resistance, voltage	100 kΩ	Input voltage	0...10 V
Number of inputs	1	Voltage drop	< 0.1 V @ I _{IN} = 20 mA (current input)

Output

Cut-off frequency (-3 dB)	> 100 Hz	Load impedance current	≤ 500 Ω
Number of outputs	1	Output current	0...20 mA, 4...20 mA
Output voltage, note	0...10 V	load impedance voltage	≥ 10 kΩ

General data

Current-carrying capacity of cross-connect.	≤ 20 A	Galvanic isolation	3-way isolator
Input/Output	configurable	Power consumption	ca. 0.6 W
Rail	TS 35	Temperature coefficient	≤ 150 ppm/K of final value
Type of connection	Screw connection	Voltage supply	24 V DC ± 15 %

Insulation coordination

EMC standards	DIN EN 61326	Galvanic isolation	3-way isolator
Insulation voltage	500 V _{eff} / 1 s	Insulation voltage input or output/rail	500 V _{eff} / 1 s
Insulation voltage input or output/supply	500 V _{eff} / 1 s	Pollution severity	2
Rated voltage	50 V	Surge voltage category	II

Connection data

Type of connection	Screw connection	Clamping range, rated connection	2.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²

MAS DC/DC SELECT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC002653	ETIM 7.0	EC002653
ETIM 8.0	EC002653	ECLASS 9.0	27-21-01-20
ECLASS 9.1	27-21-01-90	ECLASS 10.0	27-21-01-20
ECLASS 11.0	27-21-01-20		

Approvals

Approvals



ROHS	Conform
UL File Number Search	E337701

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	STEP
Engineering Data	EPLAN, WSCAD
User Documentation	Instruction sheet
Catalogues	Catalogues in PDF-format

MAS DC/DC SELECT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Electric symbol

