

physical. chemical. biological.





P0K1.232.2I.B.050 Platinum sensor with wires










Benefits & Characteristics

- Excellent long-term stability
- Low self-heating
- Fast response time

- Long isolated wires
- Stranded wires available

Illustration¹⁾



Technical Data

Operating temperature range:	-50 °C to +200 °C
Nominal resistance:	100 Ω at 0 °C
Characteristics curve:	3850 ppm/K
Long-term stability:	< 0.04 % at 1000 h at maximal operating temperature
Tolerance class (dependent on temperature range):	IEC 60751 F0.3 B (IST AG reference)
Connection:	Cu/Ag-wire, AWG30, PTFE-insulated, 50 mm long
Dimensions:	2.3 x 2.0 x 0.65 / 1.3
Tolerance (chip):	L ±0.2 mm, W ±0.2 mm,H ±0.1 mm, H2 ±0.3 mm

Product Photo



P0K1.232.2I.B.050 1/2



physical. chemical. biological.













Order Information

Description: Item number: Former main reference: P0K1.232.2I.B.050 100443 010.00678

Additional Documents

	Document name:
Application Note:	ATP_E



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

P0K1.232.2I.B.050 2/2