
R-134G7210100CC ECN # REV DESCRIPTION DRAWN DATE CHECKD DATE APPRV				
	D DATE			
R-134G7210100CC - A RELEASED Veena 20/04/09 Suresh 20/04/09 Farne	04/05/09			



Dimensions : Millimetres

Specifications: Electrical Performance:

Impedance	: 50Ω.
Frequency range	: DC to 3GHz.
Maximum working voltage	: 60V rms.
Minimum dielectric withstanding voltage	: 200V rms.
Minimum Insulation resistance	: 500MΩ.

Specification Table

Item	Description	Part Number
1	RP-SMA B/H Jack for ϕ 1.37mm Cable (Nut x 1, Washer x 1)	
2	Heat Shrink Tube F32 ¢2.5mm L = 15.0mm Colour: Black	
3	¢1.37mm Cable Colour: Black	R-134G7210100CC
4	U.FL-LP-088 Shell for	
5	U.FL-LP-088 Terminal for \01.37mm Cable	

http://www.farnell.com

RoHS Compliant

http://www.newark.com

http://www.cpc.co.uk

(the Group) for are licensed to it, two licence is granted on the lose of other intent for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change with- out notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the prod-	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:			
	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	Veena	20/04/09	Cable Assembly - U.FL - SMA, RP, 100mm			า
		CHECKED BY:	DATE:	SIZE DWG NO.	SIZE DWG NO.	ELECTRONIC FILE 1699245-TDS DWG	REV
		Suresh	20/04/09				Α
		APPROVED BY:	DATE:				<u> </u>
		Farnell	04/05/09	SCALE: NTS U.O.M.: mm		SHEET: 1 OF	F 1