



TSic 716 TO92

Temperature Sensor IC

For a fully calibrated and extremely accurate low power temperature measurement

Benefits & Characteristics

- Easy to integrate (digital output signal)
- Outstanding accuracy of ±0.07 K
- Very low power consumption
- Fully calibrated

Illustration

Excellent long-term stability

L

- Accuracy range of 20 K can be shifted (default: +25 °C to +45 °C)
- Capable of communicating over a distance of > 10 m

L2

Technical Data

Dimensions (L / L2 x W x H in mm): $^{2)}$	17.30 / 3.81 x 4.57 x 2.3
Operating temperature range:*	-10 °C to +60 °C (-7 °C to +57 °C guaranteed)
Accuracy:*	± 0.07 K in the range of $+25$ °C to $+45$ °C
Resolution:*	4 mK
Sampling rate:*	1 Hz
Supply voltage:	4.5 V to 5.5 V
Supply current:	typ. 45 μA at 25 °C and 5 V for minimal self-heating
Packaging:*	ТО92
Output signal:	14 bit ZACWire - see application note ATTSic_E
2) For tolerances, see Application Note	




physical. chemical. biological.

Product Photo



Pin Assignment



	Pin 1	Pin 2	Pin 3
ТО92	GND	Signal	V_{dd} , Supply voltage (3 V to 5.5 V)

Absolute maximal ratings

	Min	Max
Supply voltage (V_{dd})	-0.3 V	6 V
Voltages to analog I/O – Pins (V_{SIG} , V_{GND})	-0.3 V	V _{dd} +0.3 V
Storage temperature range (T _{stor})	-10 °C	+60 °C
Non-operating temperature range		

Operating conditions

	Min	Тур	Max
Supply voltage to GND (V ⁺)	2.97 V	5 V	5.5 V
Supply current (I _{vdd}) at V _{dd} = 3.3 V, RT	30 µA	45 μΑ	80 μΑ
Operating temperature range (T _{amb})	-10 °C		+60 °C
Output load capacitance (C _L)			15 nF
External capacitance between V_{dd} and $GND^{1)}$	100 nF (recommer	nded)	
Output load resistance between signal and GND (or $V_{\rm dd}$	47 kΩ		

 $^{\mbox{\tiny 1)}}$ Recommended as close to TSic $V_{\mbox{\tiny dd}}$ and GND-Pins as possible



physical. chemical. biological.



Temperature accuracies²⁾

T1: +25 °C to +45 °C	±0.07 K
T2: -10 °C to +60 °C	±0.2 K

²⁾ The sensor is calibrated at 5 V. The provided accuracy is applicable for a supply voltage between 4.5 V and 5.5 V. The accuracy is smaller with a supply voltage between 2.97 V and 4.5 V. For applications where the best accuracy at 3 V is requested, ask for a custom specific, 3 V calibrated device. Other TSic products with custom specific calibrations are available upon request e.g. other temperature range for high accuracy. Accuracy at delivery; the assembly method can influence the accuracy!

Order Information		
Description:	Item number:	Former main reference:
TSic 716 TO92	103493	030.00048
Additional Documents		
	Document name:	
Application Note:	ATTSIC_E	



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes without previous announcement as well as mistakes reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • Typing errors and mistakes reserved • Product specifications are subject to change without notice • All rights reserved