## RF Adapter N Jack to F Plug

# multicomp PRO

RoHS

Compliant

## Descriprion


The MP008640 is a Straight nickel plated brass adaptor, with a copper, nickel plated inner conductor. This RF/coaxial inter series adaptor connects N-jack to F-plug.

## Features



## • 50R Impedance

- 250MHz Frequency
- -55 to +125°C Operating temperature range
- Multicomp Pro products are rated 4.6 out of 5 stars
- 12 month limited warranty \*view Terms & Conditions for details
- 96% of customers would recommend to a friend



### **Electrical Characteristics**

Frequency Range Insulation Resistance Dielectric Withstand Voltage Temperature Range Life

#### ics

- : DC 250MHz
- : ≥500MΩ
- : 1500V
- : -55°C to +125°C : 500 matings

No.	Description	Qty	Material	Plating
1	Body		Brass	Nickel
2	Insulator	1	PTFE	/
3	Inner Conductor		Beryllion	Nickel

Dimensions : Millimetres

## Part Number Table

Description	Part Number
RF Adapter, N Jack to F Plug, Straight Adapter	MP008640

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

