

Yodalarm

YA40

Multi-purpose Audible Signalling Device designed for use in **Commercial, Light Industrial &** Marine applications.

PRODUCT FEATURES

- Max sound output 108 dB(A) @ 1m
- IP65 rated as standard
- 32 selectable tones meeting international regulations
- Flame retardant ABS enclosure
- Stainless steel fixings
- 2 stage alarm
- · Independently selectable second stage (optional)
- Low current consumption
- Robust, reliable and simple to install

Product Approvals





Compliant



Merchant Shipping (Marine Equipment) Regulations EN 54-3:2014 incl. A1:2019, IEC 60092-504:2016 IEC 60533:2015 Module B (BSI/UK/3.53/738807) Module D (BSI/MED/UK/738808)



BS EN 54-3: 2001 + A1:2002 + A2:2006

CE

BS EN 54-3: 2001 + A1:2002 + A2:2006



Compliant

UK +44 (0) 121 446 5322 FR +33 (0) 170 721 271 uksales@moflash.co.uk



www.moflash.com

exportsales@moflash.co.uk

Ambient Conditions Operating Temperatures Standard General -35 °C to +70 °C EN54 Pt:3 Fire -25 °C to +55 °C Storage Temperature -40 °C to +70 °C Max. Relative Humidity 93% ± 3 at 40 °C

Electrical Data				
Operating Voltage	Current Draw			
24vDC	35 mA at Tone 1			
24/50vDC BT	35 mA			
48vDC	35 mA			
110vDC	55 mA			
24vAC ~	100 mA			
115vAC ~	30 mA			
230vAC ~	20 mA			
Operational Parameters	± 10% of nominal			

Mechanical Data

ABS FR UL94 5VB

Stainless Steel

IP65 (IEC60529)

Enclosure Material

External Fixings

Degree of Protection

Т	E	INI	CA	\L	DA	\T/	7

Acoustic Data					
Maximum Volume Output	108dB (A)				
Volume Control Adjustment	-18 dB (A)				
2 Stage Alarm with predetermined second stage as standard.					

Selectable second stage option available (DC units only) (2)

Mounting / Installation

For ease of installation the sounder cover is supplied loose from the mounting back box. The back box must be mounted with the two cable entries either at the top or the bottom. The back box should be mounted to a suitable flat wall, bulkhead or conduit box avoiding areas of undue vibration and using the internal fixing point options in the back box. Always use the mounting gasket supplied. The recommended fixing screws are 4.5mm Dia x 20mm Long. To maintain the IP rating of the enclosure the cable entries must be fitted with a suitably rated cable gland (Not Supplied). Max cable termination 2.5mm ².

Line Integrity on DC Systems

- For 3 wire 2 stage alarm system, monitor via reverse polarity.
- For 2 wire 2 stage alarm system, monitor via threshold, (applied voltage<1v)
 an end-of-line (E.O.L) resistor is required for line monitoring and should have
 a minimum resistance of 3k3 Ohms and 0.5 Watts, wire-wound or metal film
 type.


Multi-Stage Alarm Options


Standard units offer a 2 stage alarm system with a predetermined second stage (see Tone Table on the Installation Sheet for details) A selectable second stage option is available for DC units only with the (2) prefix code in the selection table on page 3.

Dimensional Drawing

We reserve the right to make alterations to the technical data, dimensions, weights, designs and products available without notice. The illustrations cannot be considered binding.

All Dimensions in mm [inches] - Subject to alterations





mounting dimensions

A40 SIGNALLING DEVICES

SELECTION

Version	Enclosure Colour	Rated Operational Voltage	Order Number	Art. No.	Weight (Kg)
YA40 Sounder BS EN 54 Pt:3 UKCA, CE & MED	Red Normal (RN) RAL 3001	24vDC	YA40/D/RN/WR	204330	0.25
		24vDC	YA40/D/RN/WR(2)		0.25
		48vDC	YA40/F/RN/WR	204347	0.25
		24vAC ~	YA40/I/RN/WR	245154	0.70
		115vAC ~	YA40/L/RN/WR	204354	0.81
		230vAC ~	YA40/N/RF/WR	204364	0.81
	White Normal (WN) RAL 9003	24vDC	YA40/D/WN/WR	204344	0.25
		24vDC	YA40/D/WN/WR(2)		0.25
		48vDC	YA40/F/WN/WR		0.25
		24vAC ~	YA40/I/WN/WR		0.70
		115vAC ~	YA40/L/WN/WR	245175	0.81
		230vAC ~	YA40/N/WN/WR	204866	0.81