


SMALL COMPACT THERMOSTAT


KTO 011 / KTS 011







Connection diagrams



Filter fan, Cooling equipment, Signal device

- > Large setting range
- > Small size

- > Simple to mount
- > High switching performance

The mechanical thermostats KTO 011 and KTS 011 are two state regulators used to control heaters, coolers, filter fans or signal devices.

KTO 011: Thermostat (NC); contact breaker for regulating heaters. The contact opens when temperature is rising.

KTS 011: Thermostat (NO); contact maker for regulating of filter fans and heat exchangers or for switching signal devises when temperature limit has been exceeded. The contact closes when temperature is rising.















TECHNICAL DATA


Switch temperature difference	7 K (±4 K tolerance)					
Sensor element	thermostatic bimetal					
Contact type	snap-action contact					
Service life	> 100,000 cycles					
Max. operating voltage	AC 250 V (VDE) AC 120 V (UL)					
Max. inrush current	AC 16 A for 10 sec.					
Connection	2-pole terminal, clamping torque 0.5 Nm max.: rigid wire 2.5 mm² (AWG 14) stranded wire¹ 1.5 mm² (AWG 16)					
Mounting	clip for 35 mm DIN rail, EN 60715					
Casing	plastic according to UL94 V-0, light grey					
Dimensions	60 x 33 x 43 mm					
Weight	approx. 40 g					
Fitting position	variable					
Operating/Storage temperature	-45 to +80 °C (-49 to +176 °F)					
Operating/Storage humidity	max. 90 % RH (non-condensing)					
Protection type	IP20					

¹ When connecting with wires, wire end ferrules must be used.

Important note: The contact system of the regulator is subjected to environmental influences, thus the contact resistance may change. This can lead to a voltage drop and/or self-heating of the contacts.







Setting range	Art. No.	Art. No.	Switching current/capacity max.				Approvals				
	Contact breaker (NC)	Contact maker (NO)	AC 250 V	AC 120 V	DC 24 - 72 V						
0 to +60 °C	01140.0-00	01141.0-00	10 (2) A	15 (2) A	30 W	VDE	-	-	EAC	CQC	
-10 to +50 °C	01142.0-00	01143.0-00	10 (2) A	15 (2) A	30 W	VDE	UL File No. E164102	-	EAC	CQC	
+20 to +80 °C	01159.0-00	01158.0-00	3 (2) A	3 (2) A	30 W	VDE	UL File No. E164102	CSA	EAC	CQC	
+32 to +140 °F	01140.9-00	01141.9-00	10 (2) A	15 (2) A	30 W	VDE	UL File No. E164102	CSA	EAC	CQC	
+14 to +122 °F	01142.9-00	01143.9-00	10 (2) A	15 (2) A	30 W	VDE	UL File No. E164102	CSA	EAC	CQC	
0 to +60 °C	01146.9-00	01147.9-00	10 (2) A	15 (2) A	30 W	VDE	UL File No. E164102	CSA	EAC	CQC	