



Tripletac Plus™ G44R



CE Complex Design



APPLICATIONS

Ideal for general janitorial and chemical cleaning applications.

FEATURES AND BENEFITS

Triple dip natural rubber latex gloves with full length nitrile coating for longer life.

Long flock lined cuff for protection and comfort

Good resistance to oils, fats, chemicals and detergents with good grip and sensitivity

Beaded cuff for easy donning and tear resistance.

Size	Order code
6.5 (S)	3822
7.5 (M)	3823
8.5 (L)	3824
Length 320 mm	
Thickness (double wall) 0,98 mm	



G45GY



CE Complex Design



APPLICATIONS

Ideal for general janitorial and chemical cleaning applications.

FEATURES AND BENEFITS

Triple dip natural rubber latex gloves coated with nitrile for longer life

Long flock lined cuff for protection and comfort

Good resistance to oils, fats, chemicals and detergents with good grip and sensitivity

Beaded cuff for easy donning and tear resistance.

Size	Order code
6.5 (S)	10002596
7.5 (M)	10002597
8.5 (L)	10002598
9.5 (XL)	10002599
10.5 (XXL)	10002600
Length 320 mm	
Thickness (double wall) 1.00 mm	



G12P, G12T & G12Y



CE Complex Design



APPLICATIONS

Ideal for janitorial colour coding systems i.e. yellow in kitchens, pink in washrooms etc.

FEATURES AND BENEFITS

Flock lined lightweight natural rubber glove

For use in low hazard areas

Range comprises three different colours; G12P - pink, G12T tangerine and G12Y - yellow

Beaded cuff for tear resistance and easy pull on

21 CFR (USA) compliant for food applications.

Size	Order code
G12P	
6.5 (S)	1710
7.5 (M)	1711
8.5 (L)	1712
9.5 (XL)	3819
G12T	
6.5 (S)	6660
7.5 (M)	6661
8.5 (L)	6662
9.5 (XL)	6663
G12Y	
6.5 (S)	1716
7.5 (M)	1717
8.5 (L)	1718
9.5 (XL)	3821
Length 300 mm	
(double wall) 0.85mm	