



GRM-KIT-OVER100-DE-C

0805-1210 over 100uF

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Remarks	Qty
1	GRM21BR60E107ME15	2012M/0805	X5R	2.5Vdc	100µF	±20%	1.45max	85degC	20
2	GRM21BR60G107ME11	2012M/0805	X5R	4Vdc	100µF	±20%	1.45max	85degC	20
3	GRM31CR60G107MEA8	3216M/1206	X5R	4Vdc	100µF	±20%	1.9max	85degC	20
4	GRM21BR60J107ME15	2012M/0805	X5R	6.3Vdc	100µF	±20%	1.45max	85degC	20
5	GRM31CR60J107MEA8	3216M/1206	X5R	6.3Vdc	100µF	±20%	1.9max	85degC	20
6	GRM31CR61A107MEA8	3216M/1206	X5R	10Vdc	100µF	±20%	1.9max	85degC	20
7	GRM32ER61A107ME20	3225M/1210	X5R	10Vdc	100µF	±20%	2.7max	85degC	20
8	GRM31CR60E227ME11	3216M/1206	X5R	2.5Vdc	220µF	±20%	1.9max	85degC	20
9	GRM31CR60G227ME11	3216M/1206	X5R	4Vdc	220µF	±20%	1.9max	85degC	20
10	GRM32ER60G227ME05	3225M/1210	X5R	4Vdc	220µF	±20%	2.8max	85degC	20
11	GRM31CR60J227ME11	3216M/1206	X5R	6.3Vdc	220µF	±20%	1.9max	85degC	20
12	GRM32ER60J227ME05	3225M/1210	X5R	6.3Vdc	220µF	±20%	2.8max	85degC	20
13	GRM32ER60E337ME05	3225M/1210	X5R	2.5Vdc	330µF	±20%	2.8max	85degC	20
14	GRM32ER60G337ME05	3225M/1210	X5R	4Vdc	330µF	±20%	2.8max	85degC	20
15	GRM21BC80E107ME15	2012M/0805	X6S	2.5Vdc	100µF	±20%	1.45max	105degC	20
16	GRM21BC80G107ME15	2012M/0805	X6S	4Vdc	100µF	±20%	1.45max	105degC	20
17	GRM31CD80G107MEA8	3216M/1206	X6T	4Vdc	100µF	±20%	1.9max	105degC	20
18	GRM31CD80J107MEA8	3216M/1206	X6T	6.3Vdc	100µF	±20%	1.9max	105degC	20
19	GRM31CC80E227ME11	3216M/1206	X6S	2.5Vdc	220µF	±20%	1.9max	105degC	20
20	GRM32EC80E227ME05	3225M/1210	X6S	2.5Vdc	220µF	±20%	2.8max	105degC	20
21	GRM31CC80G227ME11	3216M/1206	X6S	4Vdc	220µF	±20%	1.9max	105degC	20
22	GRM32EC80G227ME05	3225M/1210	X6S	4Vdc	220µF	±20%	2.8max	105degC	20
23	GRM32EC80E337ME05	3225M/1210	X6S	2.5Vdc	330µF	±20%	2.8max	105degC	20
24	GRM31CE70G107MEA8	3216M/1206	X7U	4Vdc	100µF	±20%	1.9max	125degC	20
25	GRM32EC70G107ME15	3225M/1210	X7S	4Vdc	100µF	±20%	2.7max	125degC	20
26	GRM32EC70J107ME15	3225M/1210	X7S	6.3Vdc	100µF	±20%	2.7max	125degC	20