

SAFETY DATA SHEET

Clear Protective Lacquer

According to Preparation of Safety Data Sheets for Hazardous Chemicals Code of Practice, February 2016

SECTION 1: Identification: Product identifier and chemical identity

Product identifier

Product name Clear Protective Lacquer

Product No. CPL-b, ECPL05L, ZE

Relevant identified uses of the substance or mixture and uses advised against

Application Appliance protection.

Uses advised against No specific uses advised against are identified.

Details of the supplier of the safety data sheet

Supplier ELECTROLUBE. A division of HK WENTWORTH LTD
 H K WENTWORTH PTY LIMITED
 P.O. BOX 7336
 WARRINGAH MALL
 BROOKVALE, NSW 2100
 AUSTRALIA

SYNERGY ELECTRONICS LTD
 39 RICHARD PEARSE DRIVE
 AIRPORT OAKS
 AUCKLAND 3045

AUSTRALIA TEL: +61 (0) 2 9938 1566, FAX: +61 (0) 2 9938 1467
 NEW ZEALAND TEL: +64 (0) 9 836 6588, FAX +64 (0) 9 836 9169
 sales@hkwentworth.com.au

Emergency telephone number

Emergency telephone IN CASE OF EMERGENCY CALL:
 +61 2 8014 4558 (Australia) (24hr, Provided by Carechem 24)
 +64 9 929 1483 (New Zealand) (24hr, Provided by Carechem 24)

SECTION 2: Hazard(s) identification

Classification of the substance or mixture


Physical hazards Flam. Liq. 2 - H225

Health hazards Skin Irrit. 2 - H315 Eye Irrit. 2A - H319 Skin Sens. 1 - H317 STOT SE 3 - H336

Environmental hazards Not Classified

Label elements

Hazard pictograms



Clear Protective Lacquer

Signal word	DANGER
Hazard statements	H225 Highly flammable liquid and vapour. H315 Causes skin irritation. H319 Causes serious eye irritation. H317 May cause an allergic skin reaction. H336 May cause drowsiness or dizziness.
Precautionary statements	P210 Keep away from heat/ sparks/ open flames/ hot surfaces. - No smoking. P240 Ground/ bond container and receiving equipment. P241 Use explosion-proof electrical equipment. P242 Use only non-sparking tools. P243 Take precautionary measures against static discharge. P261 Avoid breathing vapour/ spray. P264 Wash contaminated skin thoroughly after handling. P271 Use only outdoors or in a well-ventilated area. P272 Contaminated work clothing should not be allowed out of the workplace. P280 Wear protective gloves/ protective clothing/ eye protection/ face protection. P302+P352 IF ON SKIN: Wash with plenty of soap and water. P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/ shower. P304+P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P312 Call a POISON CENTER or doctor/ physician if you feel unwell. P321 Specific treatment (see medical advice on this label). P332+P313 If skin irritation occurs: Get medical advice/ attention. P333+P313 If skin irritation or rash occurs: Get medical advice/ attention. P337+P313 If eye irritation persists: Get medical advice/ attention. P362+P364 Take off contaminated clothing and wash before reuse. P370+P378 In case of fire: Use foam, carbon dioxide, dry powder or water fog for extinction. P403+P233 Store in a well-ventilated place. Keep container tightly closed. P403+P235 Store in a well-ventilated place. Keep cool. P405 Store locked up. P501 Dispose of contents/ container in accordance with national regulations.
Contains	Propan-2-ol, Resin acids and Rosin acids, fumarated, esters with glycerol

Other hazards

This product does not contain any substances classified as PBT (persistent, bioaccumulative and toxic) or vPvB (very persistent and very bioaccumulative).

SECTION 3: Composition and information on ingredients

Mixtures

Propan-2-ol	60-100%
CAS number: 67-63-0	
Classification Flam. Liq. 2 - H225 Eye Irrit. 2A - H319 STOT SE 3 - H336	

Clear Protective Lacquer

xylene CAS number: 1330-20-7	10-30%
Classification Flam. Liq. 3 - H226 Acute Tox. 4 - H312 Acute Tox. 4 - H332 Skin Irrit. 2 - H315	
Resin acids and Rosin acids, fumarated, esters with glycerol CAS number: 97489-11-7	10-30%
Classification Eye Irrit. 2A - H319 Skin Sens. 1 - H317 Aquatic Chronic 4 - H413	

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

Description of first aid measures

General information	Get medical attention immediately. Show this Safety Data Sheet to the medical personnel.
Inhalation	Remove affected person from source of contamination. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Place unconscious person on their side in the recovery position and ensure breathing can take place.
Ingestion	Rinse mouth thoroughly with water. Remove any dentures. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Do not induce vomiting unless under the direction of medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Never give anything by mouth to an unconscious person. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Place unconscious person on their side in the recovery position and ensure breathing can take place. Maintain an open airway. Loosen tight clothing such as collar, tie or belt.
Skin Contact	It is important to remove the substance from the skin immediately. In the event of any sensitisation symptoms developing, ensure further exposure is avoided. Remove contamination with soap and water or recognised skin cleansing agent. Get medical attention if symptoms are severe or persist after washing.
Eye contact	Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 10 minutes.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue. If it is suspected that volatile contaminants are still present around the affected person, first aid personnel should wear an appropriate respirator or self-contained breathing apparatus. Wash contaminated clothing thoroughly with water before removing it from the affected person, or wear gloves. It may be dangerous for first aid personnel to carry out mouth-to-mouth resuscitation.

Most important symptoms and effects, both acute and delayed

Clear Protective Lacquer

General information	See Section 11 for additional information on health hazards. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.
Ingestion	May cause sensitisation or allergic reactions in sensitive individuals. May cause irritation.
Skin contact	May cause skin sensitisation or allergic reactions in sensitive individuals. Redness. Irritating to skin.
Eye contact	Irritating to eyes.

Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically. May cause sensitisation or allergic reactions in sensitive individuals.
-----------------------------	--

SECTION 5: Firefighting measures

Extinguishing media

Suitable extinguishing media	The product is flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

Special hazards arising from the substance or mixture

Specific hazards	Containers can burst violently or explode when heated, due to excessive pressure build-up. Flammable liquid and vapour. Vapours may be ignited by a spark, a hot surface or an ember. Vapours may form explosive mixtures with air. Fire-water run-off in sewers may create fire or explosion hazard.
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

Advice for firefighters

Protective actions during firefighting	Avoid breathing fire gases or vapours. Evacuate area. Keep upwind to avoid inhalation of gases, vapours, fumes and smoke. Ventilate closed spaces before entering them. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to Australia/New Zealand Standards AS/NZS 4967 (for clothing) AS/NZS 1801 (for helmets), AS/NZS 4821 (for protective boots), AS/NZS 1801 (for protective gloves) will provide a basic level of protection for chemical incidents.

Hazchem Code	•3YE
---------------------	------

SECTION 6: Accidental release measures

Personal precautions, protective equipment and emergency procedures

Clear Protective Lacquer

Personal precautions

No action shall be taken without appropriate training or involving any personal risk. Keep unnecessary and unprotected personnel away from the spillage. Wear protective clothing as described in Section 8 of this safety data sheet. Follow precautions for safe handling described in this safety data sheet. Wash thoroughly after dealing with a spillage. Ensure procedures and training for emergency decontamination and disposal are in place. Do not touch or walk into spilled material. Evacuate area. Provide adequate ventilation. No smoking, sparks, flames or other sources of ignition near spillage. Promptly remove any clothing that becomes contaminated. Avoid inhalation of vapours and spray/mists. Use suitable respiratory protection if ventilation is inadequate. Avoid contact with skin and eyes.

Environmental precautions

Environmental precautions

Large Spillages: Inform the relevant authorities if environmental pollution occurs (sewers, waterways, soil or air).

Methods and material for containment and cleaning up

Methods for cleaning up

Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Eliminate all ignition sources if safe to do so. No smoking, sparks, flames or other sources of ignition near spillage. Do not allow material to enter confined spaces, due to the risk of explosion. Approach the spillage from upwind. Small Spillages: If the product is soluble in water, dilute the spillage with water and mop it up. Alternatively, or if it is not water-soluble, absorb the spillage with an inert, dry material and place it in a suitable waste disposal container. Large Spillages: If leakage cannot be stopped, evacuate area. Flush spilled material into an effluent treatment plant, or proceed as follows. Contain and absorb spillage with sand, earth or other non-combustible material. Place waste in labelled, sealed containers. Clean contaminated objects and areas thoroughly, observing environmental regulations. The contaminated absorbent may pose the same hazard as the spilled material. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

Reference to other sections

Reference to other sections

For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

SECTION 7: Handling and storage, including how the chemical may be safely used

Precautions for safe handling

Usage precautions

Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. The product is flammable. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. In use may form flammable/explosive vapour-air mixture. Vapours may accumulate on the floor and in low-lying areas. Use explosion-proof electrical, ventilating and lighting equipment. Use only non-sparking tools. Take precautionary measures against static discharges. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.

Advice on general occupational hygiene

Wash promptly if skin becomes contaminated. Take off contaminated clothing and wash before reuse. Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Wash at the end of each work shift and before eating, smoking and using the toilet. Change work clothing daily before leaving workplace.

Conditions for safe storage, including any incompatibilities

Clear Protective Lacquer

Storage precautions

Store away from incompatible materials (see Section 10). Store in accordance with local regulations. Eliminate all sources of ignition. Take precautionary measures against static discharges. Earth container and transfer equipment to eliminate sparks from static electricity. Keep away from oxidising materials, heat and flames. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage. Bund storage facilities to prevent soil and water pollution in the event of spillage. The storage area floor should be leak-tight, jointless and not absorbent.

Storage class

Flammable liquid storage.

Specific end use(s)

Specific end use(s)

The identified uses for this product are detailed in Section 1.

SECTION 8: Exposure controls and personal protection

Control parameters

Occupational exposure limits

Propan-2-ol

Long-term exposure limit (8-hour TWA): 400 ppm 983 mg/m³

Short-term exposure limit (15-minute): 500 ppm 1230 mg/m³

Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation. Personal, workplace environment or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Use process enclosures, local exhaust ventilation or other engineering controls as the primary means to minimise worker exposure. Personal protective equipment should only be used if worker exposure cannot be controlled adequately by the engineering control measures. Ensure control measures are regularly inspected and maintained. Ensure operatives are trained to minimise exposure. The engineering controls also need to keep gas, vapour or dust concentrations below any lower explosive limits. Use explosion-proof ventilating equipment.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Personal protective equipment for eye and face protection should comply with Australia/New Zealand Standard AS/NZS 1337. Wear tight-fitting, chemical splash goggles or face shield. If inhalation hazards exist, a full-face respirator may be required instead.

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. The most suitable glove should be chosen in consultation with the glove supplier/manufacture, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with Australia/New Zealand Standard AS/NZS 2161. Considering the data specified by the glove manufacturer, check during use that the gloves are retaining their protective properties and change them as soon as any deterioration is detected. Frequent changes are recommended.

Other skin and body protection

Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.

Clear Protective Lacquer

Hygiene measures	Provide eyewash station and safety shower. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reuse. Clean equipment and the work area every day. Good personal hygiene procedures should be implemented. Wash at the end of each work shift and before eating, smoking and using the toilet. When using do not eat, drink or smoke. Preventive industrial medical examinations should be carried out. Warn cleaning personnel of any hazardous properties of the product.
Respiratory protection	Respiratory protection complying with an approved standard should be worn if a risk assessment indicates inhalation of contaminants is possible. Ensure all respiratory protective equipment is suitable for its intended use and complies with Australia/New Zealand Standard AS/NZS 1716. Check that the respirator fits tightly and the filter is changed regularly. Gas and combination filter cartridges should comply with Australia/New Zealand Standard AS/NZS 1716. Full face mask respirators with replaceable filter cartridges should comply with Australia/New Zealand Standard AS/NZS 1716. Half mask and quarter mask respirators with replaceable filter cartridges should comply with Australia/New Zealand Standard AS/NZS 1716.
Environmental exposure controls	Keep container tightly sealed when not in use.

SECTION 9: Physical and chemical properties

Information on basic physical and chemical properties

Appearance	Liquid.
Colour	Light (or pale).
Odour	Solvent.
Odour threshold	Not available.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	12°C Closed cup.
Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Flammability Limit - Lower(%)	Not available.
Other flammability	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	Not available.
Bulk density	0.86 kg/l
Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.

Clear Protective Lacquer

Viscosity	25 mPa s @ 20°C
Explosive properties	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.
Volatile organic compound	This product contains a maximum VOC content of 79 %.

SECTION 10: Stability and reactivity

Reactivity	See the other subsections of this section for further details.
Stability	Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.
Possibility of hazardous reactions	The following materials may react strongly with the product: Oxidising agents.
Conditions to avoid	Avoid heat, flames and other sources of ignition. Containers can burst violently or explode when heated, due to excessive pressure build-up. Static electricity and formation of sparks must be prevented. Do not pressurise, cut, weld, drill, grind or otherwise expose containers to heat or sources of ignition.
Materials to avoid	Oxidising materials. Acids - oxidising.
Hazardous decomposition products	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

SECTION 11: Toxicological information

Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

ATE dermal (mg/kg) 6,586.83

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

ATE inhalation (vapours mg/l) 165.1

Skin corrosion/irritation

Animal data Irritating.

Serious eye damage/irritation

Serious eye damage/irritation Causes serious eye irritation.

Respiratory sensitisation

Respiratory sensitisation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation May cause skin sensitisation or allergic reactions in sensitive individuals.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Clear Protective Lacquer

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity None of the ingredients are listed or exempt.

Reproductive toxicity

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure STOT SE 3 - H336 May cause drowsiness or dizziness.

Target organs Central nervous system

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Based on available data the classification criteria are not met.

General information The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.

Ingestion May cause sensitisation or allergic reactions in sensitive individuals. May cause irritation.

Skin Contact May cause skin sensitisation or allergic reactions in sensitive individuals. Redness. Irritating to skin.

Eye contact Irritating to eyes.

Route of exposure Ingestion Inhalation Skin and/or eye contact

Target Organs Central nervous system

Medical considerations Skin disorders and allergies.

SECTION 12: Ecological information

Ecotoxicity Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

Toxicity Based on available data the classification criteria are not met.

Persistence and degradability

Persistence and degradability The degradability of the product is not known.

Bioaccumulative potential

Bioaccumulative Potential No data available on bioaccumulation.

Partition coefficient Not available.

Mobility in soil

Mobility No data available.

Other adverse effects

Clear Protective Lacquer

Other adverse effects None known.

SECTION 13: Disposal considerations

Waste treatment methods

General information

The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. Disposal of this product, process solutions, residues and by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any local authority requirements. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.

Disposal methods

Do not empty into drains. Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste, residues, empty containers, discarded work clothes and contaminated cleaning materials should be collected in designated containers, labelled with their contents. Incineration or landfill should only be considered when recycling is not feasible. Vapour from residual product may create a highly flammable or explosive atmosphere inside the container. Containers should be thoroughly emptied before disposal because of the risk of an explosion. Do not cut or weld used containers unless they have been thoroughly cleaned internally.

SECTION 14: Transport information

General

For limited quantity packaging/limited load information, consult the relevant modal documentation using the data shown in this section.

UN number

UN No. (ADG) 1263

UN No. (IMDG) 1263

UN No. (ICAO) 1263

UN proper shipping name

Proper shipping name (ADG) PAINT

Proper shipping name
(IMDG) PAINT

Proper shipping name (ICAO) PAINT

Transport hazard class(es)

ADG class 3

ADG classification code F1

ADG label 3

IMDG class 3

ICAO class/division 3

Transport labels



Packing group

Clear Protective Lacquer

ADG packing group II

IMDG packing group II

ICAO packing group II

Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

Special precautions for user

Always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

EmS F-E, S-E

Hazchem Code •3YE

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78
and the IBC Code

SECTION 15: Regulatory information

Inventories

Australia - AICS

None of the ingredients are listed or exempt.

SECTION 16: Any other relevant information

Abbreviations and acronyms used in the safety data sheet ADG: Australian dangerous goods code

IATA: International air transport association.

ICAO: Technical instructions for the safe transport of dangerous goods by air.

IMDG: International maritime dangerous goods.

CAS: Chemical abstracts service.

ATE: Acute toxicity estimate.

LC₅₀: Lethal concentration to 50 % of a test population.

LD₅₀: Lethal dose to 50% of a test population (median lethal dose).

EC₅₀: 50% of maximal effective concentration.

PBT: Persistent, bioaccumulative and toxic substance.

vPvB: Very persistent and very bioaccumulative.

Classification abbreviations and acronyms

Flam. Liq. = Flammable liquid

Eye Irrit. = Eye irritation

Skin Irrit. = Skin irritation

Skin Sens. = Skin sensitisation

STOT SE = Specific target organ toxicity-single exposure

Training advice

Read and follow manufacturer's recommendations. Only trained personnel should use this material.

Issued by

Emily Kirk

Revision date

20/11/2019

Revision

1.1

Clear Protective Lacquer

SDS No. 982

Hazard statements in full

- H225 Highly flammable liquid and vapour.
- H226 Flammable liquid and vapour.
- H312 Harmful in contact with skin.
- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H319 Causes serious eye irritation.
- H332 Harmful if inhaled.
- H336 May cause drowsiness or dizziness.
- H413 May cause long lasting harmful effects to aquatic life.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.