


PicoScope® 2200A Series

Benchtop performance in a pocket-sized scope



2 channels
Low cost
200 MHz bandwidth
Up to 1 GS/s sampling rate
Arbitrary waveform generator
Advanced digital triggers
Persistence display modes
USB connected and powered
Mask limit testing
Serial bus decoding

Supplied with SDK including example programs
Free technical support
Free software upgrades
Software compatible with
Windows XP, Windows Vista,
Windows 7 and Windows 8

Powerful, portable, and versatile

The PicoScope 2200A Series oscilloscopes offer a small, light, modern alternative to bulky benchtop devices. You can now fit a 200 MHz, 1 GS/s instrument easily in your laptop bag! They are perfect for engineers on the move, and ideal for a wide range of applications including design, test, education, service, monitoring, fault finding, and repair.

A small form factor is not the only benefit of these PC-based scopes. With our PicoScope 6 software, high-end features such as serial decoding and mask limit testing are included as standard. New functionality is regularly delivered through free upgrades, optimized with the help of feedback from our customers.





The USB connection makes printing, copying, saving, and emailing your data from the field quick and easy. The high-speed USB interface

allows fast data transfer, while USB powering removes the need to carry around a bulky external power supply.




Fast sampling

The PicoScope 2200A Series oscilloscopes provide fast real-time sampling rates up to 1 GS/s, equivalent to a timing resolution of only 1 ns. For repetitive signals, equivalent-time sampling (ETS) mode can boost the maximum effective sampling rate up to 10 GS/s, allowing even finer resolution down to 100 ps. All scopes support pre-trigger and post-trigger capture.

Arbitrary waveform and function generators

All PicoScope 2200A Series oscilloscopes have a built-in arbitrary waveform generator (AWG). Waveforms can be imported from data files or created and modified using the built-in graphical AWG editor.

A function generator is also included, with sine, square, triangle, DC level and many more standard waveforms. As well as level, offset and frequency controls, advanced options allow you to sweep over a range of frequencies. Combined with the spectrum peak hold option, this creates a powerful tool for testing amplifier and filter responses.




Digital triggering

Most digital oscilloscopes still use an analog trigger architecture based on comparators. This can cause time and amplitude errors that cannot always be calibrated out. The use of comparators often limits the trigger sensitivity at high bandwidths and can also create a long trigger rearm delay.

For over 20 years Pico have been pioneering the use of full digital triggering using the actual digitized data. This reduces trigger errors and allows our oscilloscopes to trigger on the smallest signals, even at the full bandwidth. All triggering is digital, resulting in high threshold resolution within programmable hysteresis and optimal waveform stability.

On selected models, the reduced rearm delay provided by digital triggering, together with segmented memory, allows the capture of events that happen in rapid sequence. At the fastest timebase, rapid triggering can capture a new waveform every 2 microseconds until the buffer is full. The mask limit testing function helps to detect waveforms that fail to meet your specifications.



Advanced triggers

As well as the standard range of triggers found on most oscilloscopes, the PicoScope 2200A Series offers one of the best selections of advanced triggers available. These include pulse width, windowed and dropout triggers to help you find and capture your signal quickly.




High signal integrity

Most oscilloscopes are built down to a price. PicoScopes are built up to a specification.

Careful front-end design and shielding reduces noise, crosstalk and harmonic distortion. Decades of oscilloscope design experience can be seen in improved pulse response and bandwidth flatness. We are proud of the dynamic performance of our products and publish these specifications in detail. The result is simple: when you probe a circuit, you can trust in the waveform you see on the screen.

Color persistence modes


Advanced display modes allow you to see old and new data superimposed, with new data in a brighter color or shade. This makes it easy to see glitches and dropouts and to estimate their relative frequency. Choose between analog persistence, digital color, or custom display modes.



Spectrum analyzer

With the click of a button, you can open a new window to display a spectrum plot of selected channels up to the full bandwidth of the oscilloscope. A comprehensive range of settings gives you control over the number of spectrum bands, window types and display modes.

PicoScope software allows you to display multiple spectrum views with different channel selections and zoom factors, and see these alongside time-domain waveforms of the same data. A comprehensive set of automatic frequency-domain measurements can be added to the display, including THD, THD+N, SINAD, SNR and IMD. You can even use the AWG and spectrum mode together to perform swept scalar network analysis.




Automatic measurements


PicoScope allows you to automatically display a table of calculated measurements for troubleshooting and analysis. Using the built-in measurement statistics you can see the average, standard deviation, maximum and minimum of each measurement as well as the live value.

You can add as many measurements as you need on each view. Each measurement includes statistical parameters showing its variability.

For information on the measurements available in scope and spectrum modes, see **Automatic Measurements** in the **Specifications** table.



15 scope mode measurements



11 spectrum mode measurements


Serial decoding

The PicoScope 2200A Series oscilloscopes include serial decoding capability as standard. The decoded data can be displayed in the format of your choice: **in view, in window,** or both at once.

- **In view** format shows the decoded data beneath the waveform on a common time axis, with error frames marked in red. These frames can be zoomed to investigate noise or distortion.
- In window format shows a list of the decoded frames, including the data and all flags and identifiers. You can set up filtering conditions to display only the frames you are interested in, search for frames with specified properties, or define a start pattern to signal when the program should list the data.

It is also possible to create a spreadsheet to decode the hexadecimal data into user-defined text strings.





Math channels

With PicoScope 6 you can perform a variety of mathematical calculations on your input signals and reference waveforms.

Use the built-in list for simple functions such as addition and inversion, or open the equation editor and create complex functions involving trigonometry, exponentials, logarithms, statistics, integrals and derivatives.



High-speed data acquisition and digitizing


The supplied drivers and software development kit allow you to both write your own software and interface to popular third-party software packages such as LabVIEW and MATLAB.

The drivers support data streaming, a mode that captures gap-free continuous data over the USB port directly to the PC's RAM or hard disk at a rate of 1 to 9.6 MS/s, so you are not limited by the size of the scope's buffer memory. Sampling rates in streaming mode are subject to PC specifications and application loading.

Mask limit testing


PicoScope allows you to draw a mask around any signal with user-defined tolerances. This has been designed specifically for production and debugging environments, enabling you to compare signals. Simply capture a known good signal, draw a mask around it, and then attach the system under test. PicoScope will capture any intermittent glitches and can show a failure count and other statistics in the **Measurements** window.

The numerical and graphical mask editors can be used separately or in combination, allowing you to enter accurate mask specifications, modify existing masks, and import and export masks as files.



Custom probe settings


The custom probes menu allows you to correct for gain, attenuation, offsets and nonlinearities of probes and transducers, or convert your waveform data to different units such as current, scaled voltage, temperature, pressure, power or dB. Definitions can be saved to disk for later use. Definitions for standard Pico-supplied oscilloscope probes and current clamps are built in, and you can also create your own using linear scaling or even an interpolated data table.



High-end features as standard

Buying a PicoScope is not like making a purchase from other oscilloscope companies, where optional extras considerably increase the price. With our scopes, high-end features such as resolution enhancement, mask limit testing, serial decoding, advanced triggering, automatic measurements, math channels, XY mode, segmented memory (where available), and a signal generator are all included in the price.

To protect your investment, both the PC software and firmware inside the scope can be updated. Pico Technology have a long history of providing new features for free through software downloads. We deliver on our promises of future enhancements year after year, unlike many other companies in the field. Users of our products reward us by becoming lifelong customers and frequently recommending us to their colleagues.



	۱	_		١		_	S	_ I	۱ ـ	_	_	_	
_	r	$\boldsymbol{\frown}$	$\boldsymbol{\alpha}$			т.	C	ום	\mathbf{a}	_	г.	$\overline{}$	·r
		u	u	u	•	L	-31			_	L	u	

Model	PicoScope 2204A	PicoScope 2205A	PicoScope 2206A	PicoScope 2207A	PicoScope 2208A	
Bandwidth (-3 dB)	10 MHz	25 MHz	50 MHz	100 MHz	200 MHz	
Maximum sampling rate	100 MS/s	200 MS/s	500 MS/s	1 GS/s	1 GS/s	
Buffer memory	8 kS	16 kS	32 kS	40 kS	48 kS	
Function generator + AWG	100 kHz	100 kHz	1 MHz	1 MHz	1 MHz	

Rise time (calculated) 35 ns 14 ns 7 ns 3. Vertical resolution 8 bits	0 MHz 3.5 ns	200 MHz						
Bandwidth (-3 dB) 10 MHz 25 MHz 50 MHz 100 Rise time (calculated) 35 ns 14 ns 7 ns 3. Vertical resolution 8 bits		200 MHz						
Rise time (calculated) 35 ns 14 ns 7 ns 3. Vertical resolution 8 bits		200 MHz						
Vertical resolution 8 bits	.5 ns							
		1.75 ns						
Enhanced vertical resolution Lin to 12 bits	8 bits							
Emilianced vertical resolution Op to 12 bits	Up to 12 bits							
Input ranges ±50 mV, ±100 mV, ±200 mV, ±500 mV, ±1 V, ±2 V, ±5 V	± 50 mV, ± 100 mV, ± 200 mV, ± 500 mV, ± 1 V, ± 2 V, ± 5 V, ± 10 V, ± 20 V							
Input sensitivity 10 mV/div to 4 V/div (10 vertical divisions	10 mV/div to 4 V/div (10 vertical divisions)							
Input coupling AC / DC	AC / DC							
Input characteristics BNC, 1 M Ω 14 pF BNC, 1	·							
Analog onset range +2.5 V (500	±250 mV (50 mV to 200 mV ranges) ±2.5 V (500 mV to 2 V ranges)							
DC accuracy ±3% of full scale								
Overvoltage protection $\pm 100 \text{ V (DC + AC peak)}$								
HORIZONTAL (TIMEBASE)								
Maximum sampling rate 1 ch. 100 MS/s 200 MS/s (ChA) 500 MS/s 1	GS/s 0 MS/s	1 GS/s 500 MS/s						
Equivalent sampling rate (ETS) 2 GS/s 4 GS/s 5 GS/s 10	GS/s	10 GS/s						
Maximum sampling rate (streaming) 1 MS/s 9.6	6 MS/s							
, , , , , , , , , , , , , , , , , , , ,	5000 s/div	500 ps to 5000 s/di						
Buffer memory (shared between active channels) 8 kS 16 kS 32 kS 4	10 kS	48 kS						
2 MS per channel in PicoScope software. 100 MS (shared) in Buffer memory (streaming mode)								
Up to available PC memory when using SDI	Up to available PC memory when using SDK.							
Maximum buffers (normal triggering) 10 000								
(1 00 0/	32							
·	±50 ppm							
Sample jitter < 30 ps RMS < 5 p	< 30 ps RMS < 5 ps RMS							
DYNAMIC PERFORMANCE (typical)								
Crosstalk (full bandwidth) Better than 200:1 (equal ranges) Better than 400	Better than 200:1 (equal ranges) Better than 400:1 (equal ranges)							
Harmonic distortion < -50 dB at 100 kHz, full-scale input	< -50 dB at 100 kHz, full-scale input							
SFDR > 52 dB at 100 kHz, full-scale input	> 52 dB at 100 kHz, full-scale input							
Noise $< 150 \mu V RMS (\pm 50 mV range)$ $< 200 \mu V RMS$	$<$ 150 μ V RMS (±50 mV range) $<$ 200 μ V RMS (±50 mV range)							
Bandwidth flatness (at scope input) (+0.3 dB, -3 dB) from DC to full bandwidt	(+0.3 dB, -3 dB) from DC to full bandwidth							
TRIGGERING								
Sources Ch A, Ch B	Ch A, Ch B							
Trigger modes None, auto, repeat, single None, auto, repeat, single	None, auto, repeat, single None, auto, repeat, single, rapid (segmented memory)							
Advanced triggers Edge, window, pulse width, window pulse width, dropout, window	Edge, window, pulse width, window pulse width, dropout, window dropout, interval, logic.							
Trigger types, ETS Rising or falling edge	bandwidth							
Trigger types, ETS Trigger sensitivity Rising or falling edge Digital triggering provides 1 LSB accuracy up to full I In ETS mode, typical 10 mV p-p at full bandwi	ridth							
Digital triggering provides 1 LSB accuracy up to full l	ridth							
Trigger sensitivity Digital triggering provides 1 LSB accuracy up to full I In ETS mode, typical 10 mV p-p at full bandwi	ridth							
Trigger sensitivity Digital triggering provides 1 LSB accuracy up to full I In ETS mode, typical 10 mV p-p at full bandwi Maximum pre-trigger capture Maximum post-trigger delay Digital triggering provides 1 LSB accuracy up to full I In ETS mode, typical 10 mV p-p at full bandwi 100% of capture size 4 billion samples	vidth astest timeba	ıse						

	PicoScope 2204A	PicoScope 2205A	PicoScope 2206A	PicoScope 2207A	PicoScope 2208		
FUNCTION GENERATOR							
Standard output signals	Sine, square, triangle, DC voltage, ramp, sinc, Gaussian, half-sine						
Pseudorandom output signals	No	one		White noise, PRBS			
Standard signal frequency	DC to 1	I00 kHz		DC to 1 MHz			
Sweep modes	U	Jp, down, dual with se	lectable start/stop free	quencies and incremen	ts		
Triggering	Free-run or up to 1 billion waveform cycles or frequency sw Triggered from scope trigger or manually.						
Output frequency accuracy	±100) ppm		±50 ppm			
Output frequency resolution			< 0.01 Hz				
Output voltage range			±2 V				
Output adjustments		Any ampli	tude and offset within	±2 V range			
Amplitude flatness (typical)	< 1 dB to	100 kHz		< 0.5 dB to 1 MHz			
DC accuracy			±1% of full scale				
SFDR (typical)	> 55 dB at 1 kHz	full-scale sine wave	> 60 dE	at 10 kHz full-scale si	ne wave		
Output characteristics		Front pane	el BNC, 600 Ω output	impedance			
Overvoltage protection			±10 V				
ITRARY WAVEFORM GENERATOR							
Update rate	1.548	MS/s		20 MS/s			
Buffer size		kS		8 kS			
Resolution			12 bits				
Bandwidth	> 100) kHz		> 1 MHz			
Rise time (10% to 90%)	< 2	 2 μs		< 120 ns			
SPECTRUM ANALYZER			1				
Frequency range	DC to 10 MHz	DC to 25 MHz	DC to 50 MHz	DC to 100 MHz	DC to 200 MH		
Display modes		Mag	gnitude, average, peak	hold			
Windowing functions	Rectangular, Gaussian, triangular, Blackman, Blackman-Harris, Hamming, Hann, flat-top						
Number of FFT points			o half available buffer r		· · · · · · · · · · · · · · · · · · ·		
MATH CHANNELS				, ,			
	-x, x+v, x-v, x	*v. x/v. x^v. sart. ext	o. In. log. abs. norm. si	gn. sin. cos. tan. arcsin	. arccos, arctan.		
Functions	-x, $x+y$, $x-y$, $x+y$, x/y , x/y , sqrt, exp, ln, log, abs, norm, sign, sin, cos, tan, arcsin, arccos, arcsinh, cosh, tanh, freq, derivative, integral, min, max, average, peak, delay				elay		
Operands	A, B (input channels), T (time), reference waveforms, constants, Pi				<u> </u>		
AUTOMATIC MEASUREMENTS							
Scope mode	low	púlse width, maximu	nge, duty cycle, falling r m, minimum, peak to p	oeak, rise time, rising r	,		
Spectrum mode	Frequency at peak, amplitude at peak, average amplitude at peak, total power, THD %, THD dB, THD plus noise, SFDR, SINAD, SNR, IMD						
Statistics		Minimum, max	imum, average and sta	indard deviation			
SERIAL DECODING							
Protocols		CAN, LIN, I	² C, UART/RS-232, SP	I, I ² S, FlexRay			
MASK LIMIT TESTING							
Statistics		Pass/	fail, failure count, total	count			
DISPLAY							
Interpolation			Linear or sin(v)/v				
Persistence modes	Linear or $sin(x)/x$ Digital color, analog intensity, custom, or none						
		Digital Color	, analog intensity, east	om, or none			
GENERAL DC connectivity		LICD 2 O /LICD 1 1	and 2 O samenatible)	ICD coble included			
PC connectivity	USB 2.0 (USB 1.1 and 3.0 compatible). USB cable included.						
Power requirements	Powered from USB port						
Dimensions (including connectors)	142 x 92 x 19 mm						
Tomporature range	< 0.2 kg (7 oz)						
Temperature range	Operating: 5°C to 50°C (20°C to 30°C for stated accuracy). Storage: -20°C to +60°C.						
Humidity range							
Safety approvals	D-LIC MATEE		signed to EN 61010-1:2		4 1E CL (D		
Compliance		•	ested to meet EN6132		· · · · · · · · · · · · · · · · · · ·		
Software included	· · · · · · · · · · · · · · · · · · ·		K, example programs (•			
PicoScope software PC requirements			'ista, Windows 7 or W anish, Dutch, English, I	•			
Languages		Korean, Norwegian, Po					







Kit contents and accessories

Your PicoScope 2200A Series oscilloscope kit contains the following items:

- PicoScope 2200A Series oscilloscope
- USB cable
- Two x1/x10 passive probes (with kits PP906 to PP910)
- Quick Start Guide
- Software and reference CD

Probes

Two x1/x10 passive probes are included, chosen to match the bandwidth of your scope.

PicoScope model	Probes included (kits PP906 to PP910)	Order code	
2204A 2205A 2206A	60 MHz probes (2)	MI007	
2207A	150 MHz probes (2)	TA132	
2208A	250 MHz probes (2)	TA131	



Hand-held oscilloscopes

Also available in the PicoScope 2000 Series, the PicoScope 2104 and 2105 single-channel hand-held oscilloscopes are the ultimate in compact design. See www.picotech.com for details.



Ordering information

ORDER CODE	DESCRIPTION	GBP*	USD*	EUR*
PP917	PicoScope 2204A 10 MHz oscilloscope without probes	79	129	109
PP906	PicoScope 2204A 10 MHz oscilloscope	99	159	139
PP966	PicoScope 2205A 25 MHz oscilloscope without probes	129	209	179
PP907	PicoScope 2205A 25 MHz oscilloscope	149	249	209
PP908	PicoScope 2206A 50 MHz oscilloscope	249	409	349
PP909	PicoScope 2207A 100 MHz oscilloscope	349	579	489
PP910	PicoScope 2208A 200 MHz oscilloscope	499	819	699

^{*}Prices are correct at the time of publication. VAT not included. Please contact Pico Technology for the latest prices before ordering. For deeper memory, or higher or flexible resolution, see the PicoScope 3000, 4000 and 5000 Series oscilloscopes.

UK headquarters:
Pico Technology
James House
Colmworth Business Park
St. Neots
Cambridgeshire
PE19 8YP
United Kingdom

+44 (0) 1480 396 395 +44 (0) 1480 396 296

sales@picotech.com

US headquarters:
Pico Technology
320 N Glenwood Blvd
Tyler
Texas 75702
United States

+1 800 591 2796 +1 620 272 0981 sales@picotech.com

Errors and omissions excepted. Windows is a registered trade mark of Microsoft Corporation in the United States and other countries. Pico Technology and PicoScope are internationally registered trade marks of Pico Technology Ltd.