

MODEL 2020

DUAL INPUT DIFFERENTIAL THERMOCOUPLE THERMOMETER

FEATURES

This instrument is designed for applications requiring either direct or differential measurement. It incorporates many features such as

- *** °C / °F / °A Switchable
- *** I/P 1 , I/P 2 , DIFFERENTIAL, HOLD
- *** True arithmetic differential reading or differential result and input 1
- *** Simultaneous display of both inputs
- *** Resolution of 0.1° to 1000° autoranging
- *** Switchable thermocouple types K / T / J / R / N / E / S
- *** Infra-Red compatability
- *** Full retention of thermocouple type and temperature scale
- *** User configurable Auto Switch Off capability
- *** Overrange / Open circuit sensor indication
- *** Low battery indication
- *** Supplied complete with shock resistant rubber boot
- *** IP67 casing

The custom display allows input 1 to be shown on a secondary display whilst displaying differential measurement. Input 1 and input 2 may also be displayed simultaneously

SPECIFICATIONS

ENVIRONMENTAL

AMBIENT OPERATING RANGE	:	-30 to 50 °C
STORAGE TEMPERATURE RANGE	:	-40 to 50 °C
HUMIDITY	:	0 to 70% R.H.

ELECTRICAL

MEASUREMENT RANGES	:	K	-200 to 1372 °C
		T	-200 to 400 °C
		J	-200 to 1200 °C
		R	0 to 1767 °C
		N	-200 to 1200 °C
		E	-200 to 1000 °C
		S	0 to 1767 °C
THERMOCOUPLE TYPES	:	K T J R N E S	
INFRA-RED SENSOR (Exergen K80)	:	K80 -50 to 250 °C	
ACCURACY @23°C	:	+/- 0.1% OF READING +/- 0.2 °C	
CHARACTERISING ACCURACY	:	LESS THAN 0.05 °C	
TEMPERATURE COEFFICIENT	:	0.01% OF READING/°C	
COLD JUNCTION COMPENSATION	:	0.0075 °C/°C	
RESOLUTION	:	0.1° to 1000, 1° ABOVE 1000	
TEMPERATURE SCALES	:	°C / °F / °A	
FUNCTIONS	:	I/P1 / I/P2 / DIFFERENTIAL / HOLD	

GENERAL

BATTERY	:	PP3 9V I.E.C. 6F22
BATTERY LIFE (INTERMITTENT USE)	:	GREATER THAN 200 HOURS (ALKALINE)
WEIGHT	:	155 gms
DIMENSIONS	:	130 X 70 X 33 mm

Cross-reference for compatible probes

Suitable probes for use with this instrument

TME PART No	DESCRIPTION	APPLICATION	T/C TYPE
KP05	NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	K
TP05	NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
KP07	NEEDLE PROBE HEAVY DUTY	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	K
TP07	NEEDLE PROBE HEAVY DUTY	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
TP10	SOUS VIDE NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
KM01	LIGHT DUTY M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	K
TM01	LIGHT DUTY M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	T
KM03	M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	K
TM03	M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	T
KM04	M.I. PROBE EXTENDED LENGTH	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	K
TM04	M.I. PROBE EXTENDED LENGTH	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	T
KS01	SURFACE BAND PROBE	FAST RESPONSE SURFACE MEASUREMENT	K
TS01-S	DUAL PROBE	FOR SURFACE AND IMMERSION MEASUREMENT	
KS07	SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	K
TS04	SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	T
KS08	HIGH TEMP SURFACE PROBE	HIGH TEMPERATURE SURFACE MEASUREMENT	K
KA04	AIR TEMPERATURE PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	K
TA04	AIR TEMPERATURE PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	T
TA12	SPATULA PROBE	BETWEEN PACK PROBE	T
KH01	SOCKET IN HANDLE	HANDLE FOR USE WITH PLUG MOUNTED PROBES	K
TH01	SOCKET IN HANDLE	HANDLE FOR USE WITH PLUG MOUNTED PROBES	T
KHA02	PLUG MOUNTED AIR PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	K
THA2	PLUG MOUNTED AIR PROBE	FAST RESPONSE AIR TEMPERATURE PROBE	T
KHM01	PLUG MOUNTED M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	K
THM01	PLUG MOUNTED M.I. PROBE	GENERAL PURPOSE LIQUID/GAS MEASUREMENT	T
KHN01	PLUG MOUNTED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	K
THN01	PLUG MOUNTED NEEDLE PROBE	CORE TEMPERATURE OF SEMI-SOLID MATERIAL	T
THA12	PLUG MOUNTED SPATULA PROBE	BETWEEN PACK PROBE	T
KHS01	PLUG MOUNTED SURFACE BAND PROBE	FAST RESPONSE SURFACE MEASUREMENT	K
KHS02	PLUG MOUNTED SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	K
THS02	PLUG MOUNTED SURFACE PROBE	GENERAL PURPOSE SURFACE MEASUREMENT	T
PKHV1	HVAC KIT	PROBE KIT DESIGNED FOR THE HVAC INDUTRY	K
PKF1	FOOD KIT	PROBE KIT DESIGNED FOR THE FOOD INDUTRY	T
PKGP1	GENERAL PURPOSE KIT	PROBE KIT CONTAINING MOST POPULAR PROBES	K
TP01	CORKSCREW PROBE	PROBE DESIGNED FOR CORE TEMPERATURE OF MEAT	T
KPS10	PIPE CLAMP PROBE	PROBE DESIGNED TO BE CLAMPED ONTO PIPES	K
TFS01	FOOD SIMULANT PROBE	SIMULATES THE CORE TEMPERATURE OF FOOD IN HOT OR COLD STORAGE	