Active DI Box

PULSE



Description

Designed for use on stage or in the studio the Pulse DI-50 has been designed for low noise signal conversion.

Features

- On/Off switch
- -20dB pad for signal attenuation
- · Ground lift switch
- · 6.35mm and unbalanced XLR inputs with parallel 6.35mm output unbalanced
- Parallel 6.35mm jack unbalanced Link output
- Input Impedance: >250kR
- Load Impedance: >600R
- Balanced XLR output
- · Rugged metal chassis complete with rubber corners
- Frequency Response: 10Hz to 40kHz
- Noise: 105dB
- THD+N @ 1kHz: <0.005%
- · Power: 9V PP3 or 18-48V phantom power operation

Part Number Table

	Description	Part Number	
netres	Active DI Box	DI-50	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. PULSE is the registered trademark of Premier Farnell Limited 2019.

Newark.com/b/Pulse Farnell.com/b/Pulse sg.element14.com/b/pulse

