

TOS-Cab32 Fibre Distribution Cabinet

Art. Number 307911



Distribution box for TRIAX PLC splitters TOS xxSC, splice trays, layout pigtailed to match trunk and drop fibre cables.

Can be used as fibre optic terminations of optic access network or sub-distribution points in and outdoor.

- Plastic enclosure, flame retardant, ageing and UV resistant.
- Special screw and key for its door lock
- Mounting on wall or on pole
- Bi-layer structure of the box: bottom for splicing and upper layer for splitting and distribution
- Special lock device for outlet of drop cables
- 2 standard slots for TOS xxSC PLC splitter cassettes--> max splitting factor: 32

Technical Specifications

ORDER INFORMATION

EAN Number 5702663079113

CHARACTERISTICS

Place of Usage Splitter cassettes: 2 x 1:16 or 4 x 1:8 + 2 x splice trays

Type TOS-Cab32

OPERATIONAL

IP Housing protection class IP 65

Temperature - operating | °C -40...+80 °C

Temperature - storage | °C -40...+80 °C

MECHANICAL

Colour RAL 7035 - Light grey

Product Depth | mm 130 mm

Packaging Depth | m 0.143 m

Packaging Height | m 0.350 m



TRIAX

connecting the future

Technical Specifications

Total Weight kg	2.390 kg
Packaging Width m	0.420 m
Product Height mm	410 mm
Main material	Plastic
Net Weight kg	2.230 kg
Tara Weight kg	0.160 kg
Packaging Volume m3	0.021 m3
Product Width mm	345 mm