

HCMS-30 WPW

30W Waterproof Column Speaker Pair – White

HCMS WP column speakers combine slim and elegant look with sturdiness and quality of materials for both indoor and outdoor applications.

Housing, grille and transducers are all made of waterproof and anti-rust materials, to increase overall durability, even in hostile environments where humidity and saltiness attack strongly.

The 2-way design (with 3" woofer + 1" tweeter) and the quality of the transducers guarantee good sound quality; the power selector facilitates installation with any type of constant voltage or low impedance line.

The wall-mounting bracket allows Pan/Tilt adjustment. They are available in two size/power, and Black or White finish.



PRODUCT DETAILS

Key features

Waterproof Design (IP66), suitable for outdoor and indoor applications

Slim and elegant appearance

2-Way Design with 3" woofer and 1" Tweeter for High-Resolution Sound

Suitable for 70V/100V and Low-Impedance Lines

Multifunctional Mounting bracket with Pan/Tilt Adjustment

Power Tap Selector for Quick Choice of Input Mode

Aluminum Housing and Grille with Anti-Rust, Dustproof and Anti-Pollution Treatment

Waterproof Speakers in PP for Maximum Durability

Pure Copper Wire Line Transformer for High-Quality Audio

Specifications

Speaker Unit	2x3" woofer, 1x1" tweeter
Rated Power (RMS)	30W - 8ohm
70V Power Tap	1-2-4-8-15W
100V Power Tap	2-4-8-15-30W
Freq. Response	140Hz-20kHz
Coverge (HxV)	120°x90°
Sensitivity (1W @ 1m)	87±3dB
Max SPL (@ 1m)	102±3dB
IP Rate	IP66
Color	White (RAL 9003)
Unit Size (LxWxH)	376x109x102mm
Packing Size - 2 Units (LxWxH)	490x270x150mm
Unit Weight	3kg
Packing Weight - 2 Units	7,5kg