

187A.16CPE | 187A.CPE - Combination pliers



Description:

- Serrated flat and and oval pipe/cable gripping surfaces combined with a high performance cutting edges.
- Cutting edges designed to cleanly cut all types of wire: soft wires and modern materials to a maximum piano wire specification of: - 187A.16CPE : 1.8mm 215 kg/mm² - 187A.18CPE : 2.0mm 210 kg/mm² - 187A.20CPE : 2.2mm 205 kg/mm² - 187AP.20CPE : 2.2mm 205 kg/mm²
- 187AP features nail & screw gripping channels
- High Mechanical advantage due to off-set rivet and cutting edge geometry reducing effort.
- High durability Carbon alloy steel, with induction hardened cutting edges.
- Bi-Material ergonomic grips resistant to chemical agents featuring: - Return spring - Tether ready point (Tether point adds 10mm to nominal length)
- Chrome finish for corrosion resistance
- Made in France.



187A.16CPE

Length L [mm]

165.0

Thickness E [mm]	9.5
Head Height C [mm]	34.0
Head Width B [mm]	21.0
Weight [g]	195.0
Piano Diameter [mm]	1.8