

CNC6P1X7R1E226M250AE

TDK item description : CNC6P1X7R1E226MT***A




Application & Main Feature

Commercial grade (Soft termination (Low resistance))

Series

CNC6(3225) [EIA 1210]



Dimensions

L 3.20±0.30 mm
 W 2.50±0.30 mm
 T 2.50±0.30 mm
 B 0.50 mm min.
 G ---

Temperature Characteristic

X7R (-55 to +125 degC, ±15%)

Rated Voltage

1E (25Vdc)

Capacitance

22µF

Capacitance Tolerance

M (±20%)

DF






5 % max.

Insulation Resistance

22 Mohm min.

AEC-Q200

Not Applicable



Characterization Sheet (Multilayer Ceramic Chip Capacitors)



⚠ All specifications are subject to change without notice.

October 31, 2020