



## ATP3X150VE | ATP.VE - PROTWIST® 1,000 Volt insulated screwdrivers for Phillips® head screws



### Description:

- For improved safety, each screwdriver is tested individually at 10,000 Volt for 10 seconds VDE approved.
- Inline Hardening Process – +100% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.



	ATP3X150VE
Diameter [mm]	40.0
Diameter D1 [mm]	8.0
Length L [mm]	275.0
Length L1 [mm]	150.0
Length L2 [mm]	125.0
Length L3 [mm]	18.0
Thickness E [mm]	8.0
Weight [g]	195.0
Phillips Tip Number ["]	PH3