

391A.16VE | 391A.VE - 1,000 volt insulated electricians diagonal cutters



Standards:

NF ISO 5749, ISO 5749, DIN ISO 5749, ASME B107.500

Description:

- Snipe nose for confined space (electrical cabinets, wiring).
- Cutting edges designed to cleanly cut all types of wire: soft wires and modern materials to a maximum piano wire specification of: - 391A.14VE : 1.4mm 225 kg/mm² - 391A.16VE : 1.6mm 220 kg/mm²
- High mechanical advantage due to off-set rivet and cutting edge geometry reducing effort.
- High durability chrome-molybdenum-vanadium steel, with induction hardened cutting edges.
- Bi-Material ergonomic grips resistant to chemical agents. - Return spring - Tether ready (Tether point adds 10mm to nominal length)

	391A.16VE
Length L [mm]	165.0
Thickness E [mm]	10.0

Head Height C [mm]	21.0
Head Width B [mm]	23.5
Head Width B1 [mm]	17.0
Weight [Kg]	0.225
Cu - Diameter Max [mm]	0.7 - 3.0