




Sensors > Temperature Sensors > Thermopile Infrared Sensors



Model Number: **TSD305-1SL10**

Thermopile Infrared Sensor Type: **Digital Thermopile Component**

Thermopile Infrared Sensor Package: **TO-5**

Thermopile Infrared Sensor Wire Length: **13.5 mm [ .52 in ]**

Optics: **Silicon Lens**

## Features

### Product Type Features

Wire/Cladding Type	Metal Pin
Model Number	TSD305-1SL10
Thermopile Infrared Sensor Type	Digital Thermopile Component
Filter Type	Blank Silicon

### Dimensions

Thermopile Infrared Sensor Wire Length	13.5 mm[.52 in]
Thermopile Infrared Sensor Diameter	9.1 mm[.36 in]
Thermopile Infrared Sensor Length	4.3 mm[.53 in]

### Usage Conditions

Ambient Temperature Range	-20 – 85 °C[-4 – 185 °F]
Target T_Object Range	0 – 300 °C

### Packaging Features

Thermopile Infrared Sensor Package	TO-5
------------------------------------	------

### Other

Field of View X x Y	10 °
Field of View at FWHM	10 °
Optics	Silicon Lens



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts



Also in the Series | **MEAS TS**




Digital Component Sensors(3)



Thermopile Infrared Sensors(9)

## Customers Also Bought



TE Part #5174339-5  
AMPLIMITE 050 SRS CONTACT



TE Part #3-1879071-4  
THS50 50R 5%



TE Part #2-1445088-2  
MICRO MNL HDR ASSY S/ROW AU LF



TE Part #91526-1  
CCII MR II+ REC 26-18 ASSY



TE Part #1-1419130-0  
TSC-105D3H,000



TE Part #1102855-1  
AWZG-HD.M-RSZ



TE Part #90871-1  
PROCAMP TL W/DIE COMM .093 P/S



TE Part #G-TPMO-101  
TSD305-1C55 Digital Thermopile  
Sensor



TE Part #G-TPMO-025  
TSEV01S01C05



TE Part #G-TPCO-019  
TS105-10L5.5MM