
#### R&S®ESSENTIALS

# R&S®RTC1000 OSCILLOSCOPE

**Great value** 

- ► 50 MHz to 300 MHz
- ► Two channels



Product Brochure Version 07.00 3 year warranty

#### ROHDE&SCHWARZ

Make ideas real




### AT A GLANCE

High sensitivity, multifunctionality and a great price — that is what makes the  $R\&S^{\circledcirc}RTC1000$  oscilloscope so special.

From embedded developers to service technicians to educators – the wide range of functions address a broad group of users. State-of-the-art, high-performance technology in an extremely silent design meets the high requirements of today's customers. These oscilloscopes include a wide range of upgrade options, providing true investment protection for the future.

The R&S®RTC1000 is an X-in-one instrument that offers the functionality of an oscilloscope, logic analyzer, protocol analyzer, frequency analyzer, pattern generator, function generator, digital voltmeter and component tester in a single instrument.



### **BENEFITS AND KEY FEATURES**

### Top-class hardware-based acquisition for precise measurement results

- ► Up to 2 Gsample sampling rate
- ► 2 Msample memory depth
- Low-noise measurement due to state-of-the-art A/D converters

#### Versatile measurement functions and fast results

- ► Wide selection of automatic measurement functions
- ► QuickView: key results at the press of a button
- ► Mask test: easy creation of a new mask with just a few keystrokes
- ► FFT: the easy way to analyze the signal spectrum

#### X-in-1 oscilloscope

- ▶ Oscilloscope
- Logic analyzer
- Protocol analyzer
- Waveform and pattern generator
- ▶ Digital voltmeter
- ▶ Component tester
- ► Frequency analysis mode
- ► Mask test mode
- ▶ page 6

#### Future-ready investment and scalability

- ► Free firmware updates
- Bandwidth upgrades as required
- ► Serial bus analysis options via software licenses

	R&S®RTC1000	R&S®RTB2000	R&S®RTM3000	R&S®RTA4000
Number of oscilloscope	ngo monou	HQU HIDZUUU	TIGO TITIVISUUU	IIGO IIIATUUU
channels	2	2/4	2/4	4
Bandwidth in MHz	50, 70, 100, 200, 300	70, 100, 200, 300	100, 200, 350, 500, 1000	200, 350, 500, 1000
Maximum sampling rate in Gsample/s	1/channel, 2 interleaved	1.25/channel, 2.5 interleaved	2.5/channel, 5 interleaved	2.5/channel, 5 interleaved
Maximum memory depth in Msample	1/channel, 2 interleaved	10/channel, 20 interleaved; 160 Msample (optional), segmented memory	40/channel, 80 interleaved; 400 Msample (optional), segmented memory	100/channel, 200 interleaved 1 Gsample (standard), segmented memory
Timebase accuracy in ppm	50	2.5	2.5	0.5
/ertical bits (ADC)	8	10	10	10
Minimum input sensitivity	1 mV/div	1 mV/div	500 μV/div	500 μV/div
Display	6.5", 640 × 480 pixel	10" capacitive touch, 1280 × 800 pixel	10" capacitive touch, 1280 × 800 pixel	10" capacitive touch, 1280 × 800 pixel
Jpdate rate	10 000 waveforms/s	300 000 waveforms/s in fast segmentated memory mode	2 000 000 waveforms/s in fast segmentated memory mode	2000000 waveforms/s in fas segmentated memory mode
MS0	8 channels, 1 Gsample/s	16 channels, 2.5 Gsample/s	16 channels, 5 Gsample/s	16 channels, 5 Gsample/s
Protocol (optional)	I <sup>2</sup> C, SPI, UART/RS-232/ RS-422/RS-485, CAN, LIN	I <sup>2</sup> C, SPI, UART/RS-232/ RS-422/RS-485, CAN, LIN	I <sup>2</sup> C, SPI, UART/RS-232/RS-422/ RS-485, CAN, LIN, audio (I <sup>2</sup> S/ LJ/RJ/TDM), ARINC, MIL	I <sup>2</sup> C, SPI, UART/RS-232/ RS-422/RS-485, CAN, LIN, audio (I <sup>2</sup> S), ARINC, MIL
Generator(s)	<ul><li>1 generator,</li><li>4-bit pattern generator</li></ul>	1 ARB, 4-bit pattern generator	1 ARB, 4-bit pattern generator	1 ARB, 4-bit pattern generator
Math	+,-,*,/,FFT(128k points)	+,-,*,/, FFT (128k points), 21 advanced functions	+,-,*,/,FFT(128k points), 21 advanced functions	+,-,*,/,FFT (128k points), 21 advanced functions
Rohde & Schwarz probe interface	-	-	standard	standard
RF capability	FFT	FFT	spectrum analysis 1)	spectrum analysis 1)


The R&S®RTM-K18 option is not distributed in North America.




### **EXCELLENT FEATURES**


#### Two displays instead of one

- ▶ 20 vertical divisions with virtual screen for straight-forward display of up to 13 signals
- Minimizable soft menus to enlarge horizontal waveform viewing area






### X-IN-1 OSCILLOSCOPE




#### **Oscilloscope**

With a sampling rate of up to 2 Gsample/s and a memory depth of up to 2 Msample, the R&S®RTC1000 oscilloscope excels in its class. A waveform update rate of more than 10000 waveforms/s ensures a responsive instrument that reliably catches signal faults. Included tools provide quick results, e.g. QuickView, mask tests, FFT, math, cursors and automatic measurements (including statistics).




#### Logic analyzer

The R&S°RTC-B1 option turns every R&S°RTC1000 into an intuitive-to-use MSO with eight additional digital channels. The oscilloscope captures and analyzes signals from analog and digital components in an embedded design – synchronously and time-correlated to each other. For example, the delay between the input and output of an A/D converter can be conveniently determined using the cursor measurements.




#### **Protocol analyzer**

Protocols such as I<sup>2</sup>C, SPI and CAN/LIN frequently transfer control messages between integrated circuits. The R&S®RTC1000 has versatile options for protocol-specific triggering and decoding of serial interfaces. Selective acquisition and analysis of relevant events and data is possible. With the hardware-based implementation, smooth operation and a high update rate are ensured even for long acquisitions. This is advantageous, for example, for capturing multiple packetized serial bus signals.




#### Waveform and pattern generator

The integrated R&S®RTC-B6 waveform and pattern generator up to 50 Mbit/s is useful for educational purposes and for implementing prototype hardware. In addition to common sine, square/pulse, ramp and noise waveforms, it outputs 4-bit patterns. Waveforms and patterns can be imported as CSV files or copied from oscilloscope waveforms. You can preview signals before playing them back to quickly check signal correctness. Predefined patterns for e.g. I²C, SPI, UART and CAN/LIN are provided.




#### **Digital voltmeter**

For simultaneous measurements, the R&S°RTC1000 features a three-digit digital voltmeter (DVM) and six-digit frequency counter on each channel. Provided measurement functions include DC, AC + DC (RMS) and AC (RMS).




#### **Component tester**

You will also benefit from the included component tester. A 50 Hz and a 200 Hz measuring frequency are provided to support your potentially tedious search for faulty components. And since a picture says more than a thousand words – or rather a thousand values – you will be able to tell at a glance if your error analysis is on track.



#### Frequency analysis mode

Difficult-to-find faults often result from the interaction between time and frequency signals. The FFT function of the R&S®RTC1000 is activated at the push of a button and by simply entering the center frequency and span. Thanks to the R&S®RTC1000 oscilloscopes' high-performance FFT functionality, signals can be analyzed with up to 128k points. Other practical tools include cursor measurements and autoset in the frequency domain.



#### Mask test mode

Mask tests quickly reveal whether a specific signal lies within defined tolerance limits. Masks assess the quality and stability of a DUT based on statistical pass/fail evaluation. Signal anomalies and unexpected results are quickly identified. When the mask is violated, the measurement stops. Each violation generates a pulse output at the AUX-OUT connector of the R&S®RTC1000. This pulse output can be used to trigger actions in the measurement setup.

# **OSCILLOSCOPE PORTFOLIO**

	Domain			Wulti Domain
R&S®	RTH1000	RTC1000	RTB2000	RTM3000
Vertical				
Bandwidth	60/100/200/350/500 MHz <sup>1)</sup>	50/70/100/200/300 MHz <sup>1)</sup>	70/100/200/300 MHz <sup>1)</sup>	100/200/350/500 MHz/1 GHz <sup>1)</sup>
Number of channels	2 plus DMM/4	2	2/4	2/4
Resolution	10 bit	8 bit	10 bit	10 bit
V/div 1 MΩ	2 mV to 100 V	1 mV to 10 V	1 mV to 5 V	500 μV to 10 V
V/div 50 Ω	_			500 μV to 1 V
Horizontal				
Sampling rate per channel (in Gsample/s)	1.25 (4-channel model); 2.5 (2-channel model); 5 (all channels interleaved)	1; 2 (2 channels interleaved)	1.25; 2.5 (2 channels interleaved)	2.5; 5 (2 channels interleaved)
Maximum memory (per channel/1 channel active)	125 ksample (4-channel model); 250 ksample (2-channel model); 500 ksample (50 Msample in segmented memory mode)	1 Msample; 2 Msample	10 Msample; 20 Msample (320 Msample in segmented memory mode <sup>2)</sup> )	40 Msample; 80 Msample (400 Msample in segmented memory mode <sup>2)</sup> )
Segmented memory	standard	-	option	option
Acquisition rate (in waveforms/s)	50 000	10 000	50 000 (300 000 in fast segmented memory mode <sup>2)</sup> )	64000 (2000000 in fast segmented memory mode <sup>21</sup> )
Trigger				
Options	advanced, digital trigger (14 trigger types) <sup>2)</sup>	elementary (5 trigger types)	comprehensive (7 trigger types)	comprehensive (10 trigger types)
Mixed signal option				
Number of digital channels 1)	8	8	16	16
Sampling rate of digital channels (in Gsample/s)	1.25	1	1.25	two logic probes: 2.5 on each channel; one logic probe: 5 on each channel
Memory of digital channels	125 ksample	1 Msample	10 Msample	two logic probes: 40 Msample per channel; one logic probe: 80 Msample per channel
Analysis				
Cursor meas. types	4	13	4	4
Standard meas. functions	37	31	32	32
Mask test	elementary (tolerance mask around	elementary (tolerance mask	elementary (tolerance mask	elementary (tolerance mask around
Mathematics	the signal)	around the signal)	around the signal)	the signal) basic (math on math)
Serial protocols triggering and decoding <sup>1)</sup>	elementary  I <sup>2</sup> C, SPI, UART/RS-232/RS-422/ RS-485, CAN, LIN, CAN-FD, SENT	elementary I <sup>2</sup> C, SPI, UART/RS-232/RS-422/ RS-485, CAN, LIN	l <sup>2</sup> C, SPI, UART/RS-232/RS-422/ RS-485, CAN, LIN	I <sup>2</sup> C, SPI, UART/RS-232/RS-422/RS-485, CAN, LIN, I <sup>2</sup> S, MIL-STD-1553, ARINC 429
Diaplay functions	data lagger			
Display functions  Applications 1), 2)	high-resolution frequency counter, advanced spectrum analysis, harmonics analysis, user scripting	digital voltmeter (DVM), com- ponent tester, fast Fourier trans- form (FFT)	digital voltmeter (DVM), fast Fourier transform (FFT), frequency response analysis	power, digital voltmeter (DVM), spectrum analysis and spectrogram, frequency response analysis
Compliance testing 1), 2)	-	-	-	-
Display and operation				
Size and resolution	7", color, 800 × 480 pixel	6.5", color, 640 × 480 pixel	10.1", color, 1280 × 800 pixel	10.1", color, 1280 × 800 pixel
Operation	optimized for touchscreen operation, parallel button operation	optimized for fast button operation	optimized for touchscreen operation, parallel button operation	
General data				
Dimensions in mm (W $\times$ H $\times$ D)	201 × 293 × 74	285 × 175 × 140	390 × 220 × 152	390 × 220 × 152
Weight in kg	2.4	1.7	2.5	3.3
Battery	lithium-ion, > 4 h	-	_	-

<sup>1)</sup> Upgradeable.

<sup>2)</sup> Requires an option.

Multi Domain	HD 16bit   Multi   Domain	HD 16 bit Domain	HD 16 bit
RTA4000	RTE1000	RTO6	RTP
200/250/500 MHz/1 CH=1)	200/350/500 MHz/1/1.5/2 GHz <sup>1)</sup>	600 MHz/1/2/3/4/6 GHz <sup>1)</sup>	4/6/8/13/16 GHz <sup>1)</sup>
200/350/500 MHz/1 GHz <sup>1)</sup>	2/4	4	4
10 bit	16 bit system architecture	16 bit system architecture	16 bit system architecture
500 μV to 10 V	500 µV to 10 V	1 mV to 10 V (with HD mode: 500 µV to 10 V)	
500 μV to 1 V	500 μV to 1 V	1 mV to 1 V (with HD mode: 500 µV to 1 V)	2 mV to 1 V (with HD mode: 1 mV to 1 V)
2.5; 5 (2 channels interleaved)	5	10; 20 (2 channels interleaved in 4 GHz and 6 GHz model)	20; 40 (2 channels interleaved)
100 Msample; 200 Msample (1 Gsample in segmented memory mode)	50 Msample/200 Msample	standard: 200 Msample/800 Msample; max. upgrade: 1 Gsample/2 Gsample	standard: 50 Msample/200 Msample; max. upgrade: 1 Gsample/2 Gsample
standard	standard	standard	standard
64000 (2000000 in fast segmented memory mode)	1000000 (1600000 in ultra- segmented memory mode)	1000000 (2500000 in ultra-segmented memory mode)	750 000 (3 200 000 in ultra-segmented memory mode)
comprehensive (10 trigger types)	advanced, digital trigger (13 trigger types)	advanced (includes zone trigger), digital trigger (14 trigger types)	advanced, digital trigger (14 trigger types) with real-time deembedding <sup>21</sup> , high speed serial pattern trigger incl. 8/16 Gbps CDR <sup>21</sup> , zone trigger <sup>23</sup>
16	16	16	16
two logic probes: 2.5 on each channel; one logic probe: 5 on each channel	5	5	5
two logic probes: 100 Msample per channel; one logic probe: 200 Msample per channel	100 Msample	200 Msample	200 Msample
32	47	3	3
elementary (tolerance mask around the signal)	advanced (user-configurable, hard- ware based)	47 advanced (user-configurable, hardware based)	advanced (user-configurable, hardware based)
basic (math on math)	advanced (formula editor)	advanced (formula editor)	advanced (formula editor)
I°C, SPI, UART/RS-232/RS-422/ RS-485, CAN, LIN, I°S, MIL-STD-1553, ARINC 429	I²C, SPI, UART/RS-232/ RS-422/RS-485, CAN, LIN, I²S, MIL-STD-1553, ARINC 429, FlexRay™, CAN-FD, USB 2.0/ HSIC, Ethernet, Manchester, NRZ, SENT, SpaceWire, CXPI, USB Power Delivery, automotive Ethernet 100BASE-T1	I <sup>2</sup> C, SPI, UART/RS-232/RS-422/RS-485, CAN, LIN, I <sup>2</sup> S, MIL-STD-1553, ARINC 429, FlexRay™, CAN-FD, MIPI RFFE, USB 2.0/HSIC, MDIO, 8b10b, Ethernet, Manchester, NRZ, SENT, MIPI D-PHY, SpaceWire, MIPI M-PHY/UniPro, CXPI, USB 3.1 Gen1, USB-SSIC, PCIe 1.1/2.0, USB Power Delivery, automotive Ethernet 100BASE-T1/1000BASE-T1	I <sup>2</sup> C, SPI, UART/RS-232/RS-422/RS-485, CAN, LIN, MIL-STD-1553, ARINC 429, CAN-FD, MIPI RFFE, USB 2.0/HSIC, MDIO, 8b10b, Ethernet, Manchester, NRZ, MIPI D-PHY, SpaceWire, MIPI M-PHY/UniPro, USB 3.1 Gen1/Gen2, USB-SSIC, PCIe 1.1/2.0/3.0, USB Power Delivery, automotive Ethernet 100BASE-T1/1000BASE-T1
-	histogram, trend, track <sup>2)</sup>	histogram, trend, track <sup>2)</sup>	histogram, trend, track
power, digital voltmeter (DVM), spectrum analysis and spectrogram, frequency response analysis	power, 16 bit high definition mode (standard), advanced spectrum anal- ysis and spectrogram	power, 16 bit high definition mode (standard), advanced spectrum analysis and spectrogram, jitter and noise decomposition, clock data recovery, I/O data, RF analysis, deembedding, TDR/TDT analysis	16 bit high definition mode, advanced spectrum analysis and spectrogram, jitter and noise decomposition, RF analysis, real-time deembedding, TDR/TDT analysis, I/Q data, HS serial pattern trigger with 8/16 Gbps CDR
		see data sheet (PD 5216.1640.22)	see data sheet (PD 5215.4152.22)
10.1", color, 1280 × 800 pixel	10.4", color, 1024 x 768 pixel	15.6", color, 1920 × 1080 pixel	12.1", color, 1280 × 800 pixel
optimized for touchscreen operation, par			,
000 000 150	407 040 004	450 045 004	A41 00F 01C
390 × 220 × 152	427 × 249 × 204	450 × 315 × 204	441 × 285 × 316
3.3	8.6	10.7	18
-			

# **SPECIFICATIONS IN BRIEF**

Specifications in brief		
Vertical system		
Number of channels		2
Bandwidth (–3 dB)	R&S®RTC1002 (with R&S®RTC-B220/-B221/-B222/-B223)	50 MHz/70 MHz/100 MHz/200 MHz/300 MHz
Rise time (calculated)	R&S®RTC1002 (with R&S®RTC-B220/-B221/-B222/-B223)	7 ns/5 ns/3.5 ns/1.75 ns/1.15 ns
Input impedance		1 MΩ ± 2%    14 pF ± 2 pF
Input sensitivity	maximum bandwidth in all ranges	1 mV/div to 10 V/div
DC gain accuracy	offset and position = 0, maximum operating temperature	
g	input sensitivity all ranges	3%
Acquisition system	mp at content to the first to t	
Maximum realtime sampling rate		1 Gsample/s, 2 Gsample interleaved
Acquisition memory		1 Msample, 2 Msample interleaved
Horizontal system		1 Would plot, 2 Would plot interfeaved
Timebase range		1 ns/div to 100 s/div
Trigger system		1 113/417 to 100 3/417
nigger system		edge, width, video (PAL, NTSC, SECAM, PAL-M, SDTV,
Trigger types	standard	HDTV), pattern, timeout
	option	I <sup>2</sup> C, SPI, UART/RS-232/RS-422/RS-485, CAN/LIN
Analysis and measurement function	ns	
<i>,</i>	At the push of a button, internal measurement values	nock to pook voltage noc man nock rightfull time
QuickView	are written directly onto the waveform and updated	peak-to-peak voltage, pos./neg. peak, rise/fall time, mean value, RMS value, time, frequency
	continuously.	
		burst width, count positive/negative pulses, count falling/ rising edges, mean value, RMS cycle, RMS, mean cycle,
Automated measurements		peak±, frequency, period, amplitude, base level,
		pos./neg. overshoot, pulse width, duty cycle±, rise/time,
		delay, phase
Waveform mathematics		addition, subtraction, multiplication, division, FFT
MSO option		
Digital channels		8 (1 logic probe)
Sampling rate		1 Gsample/s
Acquisition memory		1 Msample
Waveform generator option		
Resolution, sampling rate		8 bit, 978 ksample/s
Amplitude	high Z; 50 $\Omega$	60 mV to 6 V ( $V_{pp}$ ); 30 mV to 3 V ( $V_{pp}$ )
DC offset	sine	0.1 Hz to 50 kHz
	pulse/rectangle and ramp/triangle	0.1 Hz to 10 kHz
4-bit pattern generator option		
Programmable pattern	sample time	20 ns to 42 s, up/down
	memory depth	2048 sample
4-bit counter	frequency	100 mHz to 50 MHz
Square wave	frequency	1 mHz to 500 kHz
Digital voltmeter		
Measurements	DC, AC + DC (RMS), AC (RMS) resolution	up to 3 digits
Frequency counter		
Resolution		5 digits
General data		
Screen		6.5" VGA color display (640 × 480 pixel)
Interfaces		1 × USB host, USB device, LAN
Audible noise	maximum sound pressure level at a distance of 0.3 m	30.4 dB(A)
	·	285 mm × 175 mm × 140 mm
Dimensions	$W \times H \times D$	$(11.22 \text{ in} \times 6.89 \text{ in} \times 5.51 \text{ in})$
Weight		1.7 kg (3.75 lb)

# **ORDERING INFORMATION**

Designation	Туре	Order No.
R&S®RTC1000 base model		
Oscilloscope, 50 MHz, 2 channels	R&S®RTC1002	1335.7500P02
Base unit (including standard accessories: R&S®RT-ZP03S passive pagetting started manual and safety instructions)	orobe per channel, R&S®RTC-B6 wa	veform generator, power cord,
Choose your bandwidth upgrade		
Jpgrade of R&S®RTC1002 to 70 MHz bandwidth	R&S®RTC-B220	1335.7300.03
Jpgrade of R&S®RTC1002 to 100 MHz bandwidth	R&S®RTC-B221	1335.7317.03
Jpgrade of R&S®RTC1002 to 200 MHz bandwidth	R&S®RTC-B222	1335.7275.03
Jpgrade of R&S®RTC1002 to 300 MHz bandwidth	R&S®RTC-B223	1335.7323.03
Choose your options		
Mixed signal upgrade for non-MSO models, 300 MHz	R&S®RTC-B1	1335.7281.03
Naveform generator	R&S®RTC-B6	1335.7298.03
<sup>2</sup> C/SPI serial triggering and decoding	R&S®RTC-K1	1335.7230.03
JART/RS-232/RS-422/RS-485 serial triggering and decoding	R&S®RTC-K2	1335.7246.03
CAN/LIN serial triggering and decoding	R&S®RTC-K3	1335.7252.03
Application bundle, consists of the following options: R&S®RTC-K1, R&S®RTC-K2, R&S®RTC-K3, R&S®RTC-B6	R&S®RTC-PK1	1335.7330.03
Choose your additional probes		
Single-ended passive probes		
300 MHz, 10:1, 10 MΩ, 400 V, 12 pF	R&S®RT-ZP03S	1803.1001.02
500 MHz, 10 MΩ, 10:1, 300 V, 10 pF, 5 mm	R&S®RT-ZP05S	1333.2401.02
500 MHz, 10 MΩ, 10:1, 400 V, 9.5 pF	R&S®RTM-ZP10	1409.7708.02
38 MHz, 1 MΩ, 1:1, 55 V, 39 pF	R&S®RT-ZP1X	1333.1370.02
High voltage single-ended passive probes		
250 MHz, 100:1, 100 MΩ, 850 V, 6.5 pF	R&S®RT-ZH03	1333.0873.02
400 MHz, 100:1, 50 MΩ, 1000 V, 7.5 pF	R&S®RT-ZH10	1409.7720.02
400 MHz, 1000:1, 50 MΩ, 1000 V, 7.5 pF	R&S®RT-ZH11	1409.7737.02
Current probes		
20 kHz, AC/DC, 10 A/1000 A	R&S®RT-ZC02	1333.0850.02
100 kHz, AC/DC, 30 A	R&S®RT-ZC03	1333.0844.02
10 MHz, AC/DC, 150 A	R&S®RT-ZC10	1409.7750.02
100 MHz, AC/DC, 30 A	R&S®RT-ZC20	1409.7766.02
120 MHz, AC/DC, 5 A	R&S®RT-ZC30	1409.7772.02
Power supply for current probes	R&S®RT-ZA13	1409.7789.02
Active differential probes		
100 MHz, 1000:1/100:1, 8 MΩ, 1000 V (RMS), 3.5 pF	R&S®RT-ZD01	1422.0703.02
200 MHz, 10:1, 1 MΩ, 20 V diff., 3.5 pF	R&S®RT-ZD02	1333.0821.02
Logic probes		
Active 8 channel logic probe	R&S®RT-ZL03	1333.0715.02
Probe accessories		
Feedthrough termination 50 Ω	R&S®HZ22	3594.4015.02
Adapter, BNC to 4 mm dual banana	R&S®RT-ZA11	1333.0796.02
Probe pouch	R&S®RT-ZA19	1335.7875.02
Choose your accessories		
Soft case, for R&S®RTC1002 oscilloscope and accessories	R&S°RTC-Z3	1333.0867.02
Rackmount kit	R&S°ZZA-RTC1K	1333.0967.02

Service options	
Extended warranty, one year/two years	
Extended warranty with calibration coverage, one year/two years	Please contact your local Rohde & Schwarz sales office.
Extended warranty with accredited calibration coverage, one year/two years	Tionue & Jenwarz Sales Unice.

#### Service that adds value

- ▶ Worldwide
- ► Customized and flexible
- ▶ Uncompromising quality
- ► Long-term dependability

#### Rohde & Schwarz

The Rohde&Schwarz technology group is among the trailblazers when it comes to paving the way for a safer and connected world with its leading solutions in test&measurement, technology systems and networks & cybersecurity. Founded more than 85 years ago, the group is a reliable partner for industry and government customers around the globe. The independent company is headquartered in Munich, Germany and has an extensive sales and service network with locations in more than 70 countries.

www.rohde-schwarz.com

#### Sustainable product design

- ► Environmental compatibility and eco-footprint
- ► Energy efficiency and low emissions
- ► Longevity and optimized total cost of ownership

Certified Quality Management ISO 9001

Certified Environmental Management

ISO 14001

#### Rohde & Schwarz training

www.training.rohde-schwarz.com

#### Rohde & Schwarz customer support

www.rohde-schwarz.com/support



3607.4287.12 07.00 PDP/PDW 1 en