



SELTWNSPOT indicators



Eterna[®]
Everyday Lighting For Professionals



IP65 LED TWINSPOT EMERGENCY FITTING

Proven fitting with long term reliability and performance along with high ingress protection.

- Polycarbonate construction
- Twin 3W LED projectors: provide superior light output to traditional twin-spot fittings
- Horizontally and vertically adjustable heads, 180° rotation across the horizontal plane
- IP65 rating utilising high quality polycarbonate enclosure: for installation in wet or dusty environments
- Reduced battery capacity requirement: allows a more compact design reducing the weight dramatically compared to traditional products facilitating easier installation
- Minimum 3 hour non-maintained functionality in emergency mode
- Replacement battery code: EB3
- 5 year warranty

Download IES File from website

PERFECT FOR COMMERCIAL, INDUSTRIAL, WAREHOUSE & INDOOR APPLICATIONS

LEDTWNTPOT

- Individual indicator to show 'Lamps Healthy' and 'Charge'

SELTWNSPOT

- Automatic testing in accordance with EN 62034
- Individual indicator to show 'Status Indicator', 'Lamps Healthy' and 'Charge'

• M.O.M: 1 / O.P.Q: 6

Code	Version	Colour	Wattage	Colour Temp.	Lumens	Avg. Rated Life (Hrs)	IP Rating
LEDTWNTPOT	Standard	White	Twin 3W	3500K	441 lm	30,000 hrs	IP65
SELTWNSPOT	Self-Test						

