



SPECIFICATION SHEET

Product Code

CCA606

Description

13A 2 Gang Switched Socket Outlet





General Information	
Dimensions	146mm x 86mm x 9.5mm
Material composition	Rear Housing: Urea
	Front Plate: Urea
	Terminals: Brass
	Earth Strap: Mild Steel
	Terminal Screws: Brass plated steel
	Internal Busbars: Formed pressed brass
Back Box Depth	25mm – 47mm
Cable Size	4 x 2.5mm ²
Terminal Size	Live: 5mm
	Neutral: 5mm
	Earth: 5mm
Switched	Yes
Double Pole	No
Twin Earth	No
Clean Pole	No
Neon	No
Shutters	Yes
Warranty	10 Years Domestic

Standards	BS 1363-2 1995 + A4 :2012

Additional Information	Ensure that the mains supply is isolated before commencing installation.
	Bare earth cables must always be covered with appropriate sleeving and
	wired to the earth terminal.
	All white moulded accessories are manufactured using Urea
	Formaldehyde, which has similar inherent properties to antimicrobial
	additives that inhibit the growth of infectious diseases. All products
	independently tested achieved a 99.9% kill rate across all four types of the
	strains of bacteria – MRSA, E-Coli, Salmonella, and Klebsiella Pneumoniae.

V1.0