


SPECIFICATION SHEET

Product Code CCA050

Description 13A Fused Connection Unit



General Information	
Dimensions	86mm x 86mm x 9.5mm
Material composition	Front Plate: Urea Terminals: Brass Terminal Screws: Steel and Yellow Passivated Internal Busbars: Formed Press Brass Silver "On-lay" Copper/Brass Contacts
Back Box Depth	25mm – 47mm
Cable Size	4 x 2.5mm ²
Terminal Size	Live: 5mm Neutral: 5mm Earth: 5mm
Switched	No
Double Pole	No
Fuse Size	13A
Flex Outlet	Yes (Through Front of Plate)
Neon	No
Warranty	10 Years Domestic

Standards	BS 1363-4 : 1995 + A4 :2012
-----------	-----------------------------

Additional Information	<p>Ensure that the mains supply is isolated before commencing installation. Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.</p> <p>All white moulded accessories are manufactured using Urea Formaldehyde, which has similar inherent properties to antimicrobial additives that inhibit the growth of infectious diseases. All products independently tested achieved a 99.9% kill rate across all four types of the strains of bacteria – MRSA, E-Coli, Salmonella, and Klebsiella Pneumoniae.</p> <p>Flex Outlet Diameter: 10mm</p>
------------------------	--