

Page 1 of 10
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revision date / version: 22.01.2020 / 0006
Replacing version dated / version: 22.02.2019 / 0005
Valid from: 22.01.2020
PDF print date: 23.01.2020
1001® CARPET STAIN REMOVER

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

1001® CARPET STAIN REMOVER

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture:

Cleaner

Uses advised against:

No information available at present.

1.3 Details of the supplier of the safety data sheet

WD-40 Company Limited, PO Box 440, Kiln Farm, Milton Keynes, MK11 3LF, United Kingdom
Phone:+44 (0) 1908 555400, Fax:+44 (0) 1908 266900
Compliance@wd40.co.uk, www.wd40.co.uk

(IRL)

P.R. Rielly Limited KarKraft House, Kilbarrack Industrial Estate, Kilbarrack, Dublin 5, Ireland
Phone:01-832 0006, Fax:01-832 0016
web@team.ie

Qualified person's e-mail address: info@chemical-check.de, k.schnurbusch@chemical-check.de Please DO NOT use for requesting Safety Data Sheets.

1.4 Emergency telephone number

Emergency information services / official advisory body:

(IRL)

National Poisons Information Centre, Beaumont Hospital, Dublin 9, Ireland, Tel.:
+353 (0)1 809 2166 (Public Poisons Info Line, 8am-10pm, 7 days a week)
+353 (0)1 809 2566 (Info for Healthcare Professionals ONLY, 24 h, 7 days a week)

Telephone number of the company in case of emergencies:

+49 (0) 700 / 24 112 112 (WDC)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) 1272/2008 (CLP)

The mixture is not classified as dangerous in the terms of the Regulation (EC) 1272/2008 (CLP).

2.2 Label elements

Labeling according to Regulation (EC) 1272/2008 (CLP)

EUH208-Contains Reaction mass of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1), 2-methylisothiazol-3(2H)-one. May produce an allergic reaction.

2.3 Other hazards

The mixture does not contain any vPvB substance (vPvB = very persistent, very bioaccumulative) or is not included under XIII of the regulation (EC) 1907/2006 (< 0,1 %).

The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC) 1907/2006 (< 0,1 %).

SECTION 3: Composition/information on ingredients

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 22.01.2020 / 0006
 Replacing version dated / version: 22.02.2019 / 0005
 Valid from: 22.01.2020
 PDF print date: 23.01.2020
 1001® CARPET STAIN REMOVER

3.1 Substance

n.a.

3.2 Mixture

Butanedioic acid, 2(or 3)-sulfo-, 4-[2-[(1-oxododecyl)amino]ethyl] ester, sodium salt	
Registration number (REACH)	01-2119980061-44-XXXX
Index	---
EINECS, ELINCS, NLP	939-648-2 (REACH-IT List-No.)
CAS	---
content %	0,5-<5
Classification according to Regulation (EC) 1272/2008 (CLP)	Skin Irrit. 2, H315 Eye Irrit. 2, H319

For the text of the H-phrases and classification codes (GHS/CLP), see Section 16.

The substances named in this section are given with their actual, appropriate classification!

For substances that are listed in appendix VI, table 3.1 of the regulation (EC) no. 1272/2008 (CLP regulation) this means that all notes that may be given here for the named classification have been taken into account.

SECTION 4: First aid measures

4.1 Description of first aid measures

First-aiders should ensure they are protected!

Never pour anything into the mouth of an unconscious person!

Inhalation

Remove person from danger area.

Supply person with fresh air and consult doctor according to symptoms.

Skin contact

Wash thoroughly using copious water - remove contaminated clothing immediately. If skin irritation occurs (redness etc.), consult doctor.

Unsuitable cleaning product:

Solvent

Thinners

Eye contact

Remove contact lenses.

Wash thoroughly for several minutes using copious water. Seek medical help if necessary.

Ingestion

Rinse the mouth thoroughly with water.

Give copious water to drink - consult doctor immediately.

4.2 Most important symptoms and effects, both acute and delayed

If applicable delayed symptoms and effects can be found in section 11 and the absorption route in section 4.1.

The following may occur:

Irritation of the eyes

With long-term contact:

Dermatitis (skin inflammation)

In certain cases, the symptoms of poisoning may only appear after an extended period / after several hours.

4.3 Indication of any immediate medical attention and special treatment needed

n.c.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Adapt to the nature and extent of fire.

Water jet spray / alcohol resistant foam / CO2 / dry extinguisher.

Unsuitable extinguishing media

None known

5.2 Special hazards arising from the substance or mixture

In case of fire the following can develop:

Oxides of carbon

Oxides of phosphorus

Oxides of sulphur

Page 3 of 10
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revision date / version: 22.01.2020 / 0006
Replacing version dated / version: 22.02.2019 / 0005
Valid from: 22.01.2020
PDF print date: 23.01.2020
1001® CARPET STAIN REMOVER

Oxides of nitrogen
Toxic gases

5.3 Advice for firefighters

In case of fire and/or explosion do not breathe fumes.
Protective respirator with independent air supply.
According to size of fire
Full protection, if necessary.
Dispose of contaminated extinction water according to official regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Ensure sufficient supply of air.
Avoid contact with eyes or skin.
If applicable, caution - risk of slipping.

6.2 Environmental precautions

If leakage occurs, dam up.
Resolve leaks if this possible without risk.
Prevent surface and ground-water infiltration, as well as ground penetration.
Prevent from entering drainage system.
If accidental entry into drainage system occurs, inform responsible authorities.

6.3 Methods and material for containment and cleaning up

Soak up with absorbent material (e.g. universal binding agent, sand, diatomaceous earth, sawdust) and dispose of according to Section 13.
Flush residue using copious water.
Unsuitable cleaning product:
Solvent
Thinners

6.4 Reference to other sections

For personal protective equipment see Section 8 and for disposal instructions see Section 13.

SECTION 7: Handling and storage

In addition to information given in this section, relevant information can also be found in section 8 and 6.1.

7.1 Precautions for safe handling

7.1.1 General recommendations

Ensure good ventilation.
Avoid contact with eyes.
Avoid long lasting or intensive contact with skin.
Eating, drinking, smoking, as well as food-storage, is prohibited in work-room.
Observe directions on label and instructions for use.

7.1.2 Notes on general hygiene measures at the workplace

General hygiene measures for the handling of chemicals are applicable.
Wash hands before breaks and at end of work.
Keep away from food, drink and animal feedingstuffs.
Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

7.2 Conditions for safe storage, including any incompatibilities

Store product closed and only in original packing.
Not to be stored in gangways or stair wells.
Store at room temperature.

7.3 Specific end use(s)

No information available at present.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Butanedioic acid, 2(or 3)-sulfo-, 4-[2-[(1-oxododecyl)amino]ethyl] ester, sodium salt

Area of application	Exposure route / Environmental compartment	Effect on health	Descriptor	Value	Unit	Note
	Environment - freshwater		PNEC	0,019	mg/l	
	Environment - marine		PNEC	0,0019	mg/l	
	Environment - sporadic (intermittent) release		PNEC	0,19	mg/l	
	Environment - sewage treatment plant		DNEL	5	mg/l	
	Environment - sediment, freshwater		PNEC	0,0107	mg/kg	
	Environment - sediment, marine		PNEC	0,0107	mg/kg	
	Environment - sediment		PNEC	0,0103	mg/kg	
Consumer	Human - inhalation	Long term, systemic effects	DNEL	69,05	mg/m3	
Consumer	Human - dermal	Long term, systemic effects	DNEL	99,26	mg/kg bw/day	
Consumer	Human - oral	Long term, systemic effects	DNEL	2,21	mg/kg bw/day	
Workers / employees	Human - inhalation	Long term, systemic effects	DNEL	223,36	mg/m3	
Workers / employees	Human - dermal	Long term, systemic effects	DNEL	165,44	mg/kg bw/day	

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Ensure good ventilation. This can be achieved by local suction or general air extraction.

If this is insufficient to maintain the concentration under the WEL or AGW values, suitable breathing protection should be worn.

Applies only if maximum permissible exposure values are listed here.

8.2.2 Individual protection measures, such as personal protective equipment

General hygiene measures for the handling of chemicals are applicable.

Wash hands before breaks and at end of work.

Keep away from food, drink and animal feedingstuffs.

Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

Eye/face protection:

Tight fitting protective goggles (EN 166) with side protection, with danger of splashes.

Skin protection - Hand protection:

Chemical resistant protective gloves (EN 374).

If applicable

Safety gloves made of butyl (EN 374)

Protective Neoprene® / polychloroprene gloves (EN 374).

Protective nitrile gloves (EN 374).

Minimum layer thickness in mm:

>= 0,4

Permeation time (penetration time) in minutes:

>= 480

The breakthrough times determined in accordance with EN 16523-1 were not obtained under practical conditions.

The recommended maximum wearing time is 50% of breakthrough time.

Protective hand cream recommended.

Skin protection - Other:

Protective working garments (e.g. safety shoes EN ISO 20345, long-sleeved protective working garments).

Respiratory protection:

Normally not necessary.

Thermal hazards:

Not applicable

Additional information on hand protection - No tests have been performed.

In the case of mixtures, the selection has been made according to the knowledge available and the information about the contents.

Selection of materials derived from glove manufacturer's indications.

Final selection of glove material must be made taking the breakthrough times, permeation rates and degradation into account. Selection of a suitable glove depends not only on the material but also on other quality characteristics and varies from manufacturer to manufacturer.

In the case of mixtures, the resistance of glove materials cannot be predicted and must therefore be tested before use.

The exact breakthrough time of the glove material can be requested from the protective glove manufacturer and must be observed.

8.2.3 Environmental exposure controls

No information available at present.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state:	Liquid
Colour:	White
Odour:	Perfumed
Odour threshold:	Not determined
pH-value:	7-8
Melting point/freezing point:	Not determined
Initial boiling point and boiling range:	Not determined
Flash point:	Not determined
Evaporation rate:	Not determined
Flammability (solid, gas):	Not determined
Lower explosive limit:	Not determined
Upper explosive limit:	Not determined
Vapour pressure:	Not determined
Vapour density (air = 1):	Not determined
Density:	1,0-1,1 (20°C, relative density)
Bulk density:	n.a.
Solubility(ies):	Not determined
Water solubility:	Mixable
Partition coefficient (n-octanol/water):	Not determined
Auto-ignition temperature:	Not determined
Decomposition temperature:	Not determined
Viscosity:	<10 mPas
Explosive properties:	Product is not explosive.
Oxidising properties:	No

9.2 Other information

Miscibility:	Not determined
Fat solubility / solvent:	Not determined
Conductivity:	Not determined
Surface tension:	Not determined
Solvents content:	Not determined

SECTION 10: Stability and reactivity

10.1 Reactivity

The product has not been tested.

10.2 Chemical stability

Stable with proper storage and handling.

10.3 Possibility of hazardous reactions

No dangerous reactions are known.

10.4 Conditions to avoid

None known

10.5 Incompatible materials

None known

10.6 Hazardous decomposition products

No decomposition when used as directed.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Possibly more information on health effects, see Section 2.1 (classification).

12.2. Persistence and degradability:							The surfactant(s) contained in this mixture complies (comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.
12.3. Bioaccumulative potential:							n.d.a.
12.4. Mobility in soil:							n.d.a.
12.5. Results of PBT and vPvB assessment							n.d.a.
12.6. Other adverse effects:							n.d.a.

Butanedioic acid, 2(or 3)-sulfo-, 4-[2-[(1-oxododecyl)amino]ethyl] ester, sodium salt

Toxicity / effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes
12.3. Bioaccumulative potential:	Log Pow		-5,371				
Water solubility:							Soluble
12.1. Toxicity to fish:	LC50	96h	>32	mg/l	Brachydanio rerio	OECD 203 (Fish, Acute Toxicity Test)	
12.1. Toxicity to fish:	NOEC/NOEL	96h	>=32	mg/l	Brachydanio rerio	OECD 203 (Fish, Acute Toxicity Test)	
12.1. Toxicity to daphnia:	EC50	48h	19	mg/l	Daphnia magna	OECD 202 (Daphnia sp. Acute Immobilisation Test)	
12.1. Toxicity to algae:	EC50	72h	>26	mg/l	Desmodesmus subspicatus	OECD 201 (Alga, Growth Inhibition Test)	
12.2. Persistence and degradability:		28d	94	%	activated sludge	OECD 301 B (Ready Biodegradability - Co2 Evolution Test)	Readily biodegradable
12.5. Results of PBT and vPvB assessment							No PBT substance, No vPvB substance

SECTION 13: Disposal considerations

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 22.01.2020 / 0006

Replacing version dated / version: 22.02.2019 / 0005

Valid from: 22.01.2020

PDF print date: 23.01.2020

1001® CARPET STAIN REMOVER

13.1 Waste treatment methods

For the substance / mixture / residual amounts

EC disposal code no.:

The waste codes are recommendations based on the scheduled use of this product.

Owing to the user's specific conditions for use and disposal, other waste codes may be

allocated under certain circumstances. (2014/955/EU)

07 06 01 aqueous washing liquids and mother liquors

20 01 29 detergents containing hazardous substances

Recommendation:

Sewage disposal shall be discouraged.

Pay attention to local and national official regulations.

E.g. suitable incineration plant.

E.g. dispose at suitable refuse site.

For contaminated packing material

Pay attention to local and national official regulations.

Empty container completely.

Uncontaminated packaging can be recycled.

Dispose of packaging that cannot be cleaned in the same manner as the substance.

Recommended cleaner:

Water

15 01 02 plastic packaging

SECTION 14: Transport information

General statements

14.1. UN number: n.a.

Transport by road/by rail (ADR/RID)

14.2. UN proper shipping name:

14.3. Transport hazard class(es): n.a.

14.4. Packing group: n.a.

Classification code: n.a.

LQ: n.a.

14.5. Environmental hazards: Not applicable

Tunnel restriction code:

Transport by sea (IMDG-code)

14.2. UN proper shipping name:

14.3. Transport hazard class(es): n.a.

14.4. Packing group: n.a.

Marine Pollutant: n.a.

14.5. Environmental hazards: Not applicable

Transport by air (IATA)

14.2. UN proper shipping name:

14.3. Transport hazard class(es): n.a.

14.4. Packing group: n.a.

14.5. Environmental hazards: Not applicable

14.6. Special precautions for user

Unless specified otherwise, general measures for safe transport must be followed.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Non-dangerous material according to Transport Regulations.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Observe restrictions:

General hygiene measures for the handling of chemicals are applicable.

Directive 2010/75/EU (VOC): < 0,25 %

REGULATION (EC) No 648/2004

less than 5 %

anionic surfactants

phosphates

perfumes

CITRAL

CITRONELLOL

LIMONENE

LINALOOL

BENZISOTHIAZOLINONE

METHYLCHLOROISOTHIAZOLINONE/ METHYLISOTHIAZOLINONE

METHYLISOTHIAZOLINONE

Treated goods as per Regulation (EU) No. 528/2012 must display specific information on the label.

Please note Article 58 paragraph (3) subparagraph 2 of Regulation (EU) No. 528/2012.

Approval of the biocidal active substance may mean that special conditions are required for marketing the treated goods.

These are indicated in the approval of the active substance.

National rules/regulation for the compliance with maximum quantities with regard to phosphates and or phosphorous compounds must be observed and complied with.

15.2 Chemical safety assessment

A chemical safety assessment is not provided for mixtures.

SECTION 16: Other information

EUF0031

Revised sections:

2, 11, 12, 15

Classification and processes used to derive the classification of the mixture in accordance with the ordinance (EG) 1272/2008 (CLP):

Not applicable

The following phrases represent the posted Hazard Class and Risk Category Code (GHS/CLP) of the product and the constituents (specified in Section 2 and 3).

H315 Causes skin irritation.

H319 Causes serious eye irritation.

Skin Irrit. — Skin irritation

Eye Irrit. — Eye irritation

Any abbreviations and acronyms used in this document:

acc., acc. to according, according to

ADR Accord européen relatif au transport international des marchandises Dangereuses par Route (= European Agreement concerning the International Carriage of Dangerous Goods by Road)

AOX Adsorbable organic halogen compounds

approx. approximately

Art., Art. no. Article number

ASTM ASTM International (American Society for Testing and Materials)

BAM Bundesanstalt für Materialforschung und -prüfung (Federal Institute for Materials Research and Testing, Germany)

BAuA Bundesanstalt für Arbeitsschutz und Arbeitsmedizin (= Federal Institute for Occupational Health and Safety, Germany)

BSEF The International Bromine Council

bw body weight

CAS Chemical Abstracts Service

CLP Classification, Labelling and Packaging (REGULATION (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures)

CMR carcinogenic, mutagenic, reproductive toxic

DMEL Derived Minimum Effect Level

DNEL Derived No Effect Level

dw dry weight

e.g. for example (abbreviation of Latin 'exempli gratia'), for instance

EC European Community

ECHA European Chemicals Agency

EEC European Economic Community

EINECS European Inventory of Existing Commercial Chemical Substances

ELINCS European List of Notified Chemical Substances

EN European Norms
EPA United States Environmental Protection Agency (United States of America)
etc. et cetera
EU European Union
EVAL Ethylene-vinyl alcohol copolymer
Fax. Fax number
gen. general
GHS Globally Harmonized System of Classification and Labelling of Chemicals
GWP Global warming potential
IARC International Agency for Research on Cancer
IATA International Air Transport Association
IBC (Code) International Bulk Chemical (Code)
IMDG-code International Maritime Code for Dangerous Goods
incl. including, inclusive
IUCLID International Uniform Chemical Information Database
LQ Limited Quantities
MARPOL International Convention for the Prevention of Marine Pollution from Ships
n.a. not applicable
n.av. not available
n.c. not checked
n.d.a. no data available
OECD Organisation for Economic Co-operation and Development
org. organic
PBT persistent, bioaccumulative and toxic
PE Polyethylene
PNEC Predicted No Effect Concentration
ppm parts per million
PVC Polyvinylchloride
REACH Registration, Evaluation, Authorisation and Restriction of Chemicals (REGULATION (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals)
REACH-IT List-No. 9xx-xxx-x No. is automatically assigned, e.g. to pre-registrations without a CAS No. or other numerical identifier. List Numbers do not have any legal significance, rather they are purely technical identifiers for processing a submission via REACH-IT.
RID Règlement concernant le transport International ferroviaire de marchandises Dangereuses (= Regulation concerning the International Carriage of Dangerous Goods by Rail)
SVHC Substances of Very High Concern
Tel. Telephone
UN RTDG United Nations Recommendations on the Transport of Dangerous Goods
VOC Volatile organic compounds
vPvB very persistent and very bioaccumulative
wwt wet weight

The statements made here should describe the product with regard to the necessary safety precautions - they are not meant to guarantee definite characteristics - but they are based on our present up-to-date knowledge.

No responsibility.

These statements were made by:

Chemical Check GmbH, Chemical Check Platz 1-7, D-32839 Steinheim, Tel.: +49 5233 94 17 0, Fax: +49 5233 94 17 90

© by Chemical Check GmbH Gefahrstoffberatung. The copying or changing of this document is forbidden except with consent of the Chemical Check GmbH Gefahrstoffberatung.