

Type Number	6103
Designation IEC	FR10G445
System	Lithium / Iron Disulfide (Li/FeS ₂)
Shelf Life (coding)*	15 years
Nominal Voltage	1.5 V
Typical Capacity C	1100 mAh
Temperature Range	-20°C 45°C
Weight (approx.)	7,3 g

Dimensions (mm)	min	max
Ø	9.5	10.5
A	-	44.5
B	43.5	
C	4.3	-
F	-	3.8
G	0.8	

Typical Capacities (at 20°C)


Discharge Type 2s/28s,5M/H Digital still camera	Load 1200/650 mA	End Voltage [V] Pulse [n]	1.05 160
Discharge Type 1h/12h, 24h/d Digital audio	Load 50 mA	End Voltage [V] Time [h]	0.9 20

*in consideration of typical loss of capacity at storage and application

Performance Data (Typical)


Typical Discharge Curve Characteristics

Constant Current Discharge at 21°C (low and high drains)



Temperature Effects on Capacity

Constant Current Discharge



Industry Standard Testing (21°C):

Application Tests (21°C)

