

BRADY B-7425J INKJET PRINTABLE PROPYLENE LABEL STOCK

TDS No. B-7425J
Effective Date: 11/4/2021

Description:

GENERAL

Print Technology: Inkjet

Material Type: Polypropylene

Finish: Matte

Adhesive: Permanent Acrylic

APPLICATIONS

Laboratory identification such as vials, centrifuge tubes and test tubes

RECOMMENDED INK

J2000: BradyJet™ J20 series ink cartridges; cyan, magenta, and yellow

J4000: BradyJet™ J40 series ink cartridge; cyan, magenta, and yellow

B-7425J is also compatible with non-Brady inkjet printers that use pigment-based inks such as Epson® Colorworks C3500, Epson® Colorworks C6000A, Epson® Colorworks C7500G, and AstroNova® QuickLabel® QL-120D.

Customers should complete their own evaluation for fitness of use for their application. Contact Brady customer service for further information.

SPECIAL FEATURES

Brady B-7425J is an inkjet printable label material which allows for printing colored labels.

Details:

PHYSICAL PROPERTIES	TEST METHODS	TYPICAL RESULTS
Thickness	ASTM D1000 -Total (excluding liner)	0.005 inches (0.127 mm)
Adhesion to:	ASTM D1000	
-Stainless Steel	20 minute dwell 24 hour dwell	62 oz/in (63 N/100 mm) 69 oz/in (70 N/100 mm)
-Glass	20 minute dwell 24 hour dwell	56 oz/in (57 N/100 mm) 63 oz/in (64 N/100 mm)
-Polypropylene	20 minute dwell 24 hour dwell	62 oz/in (63 N/100 mm) 67 oz/in (68 N/100 mm)
Tack	ASTM D 2979 Polyken™ Probe Tack (1 second dwell, 1 cm/sec separation)	41 oz (1159 g)

ENVIRONMENTAL PERFORMANCE PROPERTIES – LABEL APPLIED TO ROOM TEMPERATURE SURFACE

B-7425J samples were printed with J20 and J40 CMY ink. B-7425J samples were adhered at room temperature to the surfaces listed below.

ENVIRONMENT	TEST METHOD	TYPICAL RESULTS
High Service Temperature	5 days at 70°C (158°F)	<ul style="list-style-type: none"> ✓ 8.5 ml glass test tube ✓ 1.5 ml polypropylene cryovial ✓ 5 ml polypropylene cryovial ✓ glass microscope slide ✓ Polyethylene bag
Low Service Temperature	5 days at -80°C (-112°F)	<ul style="list-style-type: none"> ✓ 8.5 ml glass test tube ✓ 1.5 ml polypropylene cryovial ✓ 5 ml polypropylene cryovial ✓ glass microscope slide ✓ Polyethylene bag
Simulated Incubator	3 cycles of 1 hour at 70°C (158°F) and 3 hours at room temperature	<ul style="list-style-type: none"> ✓ 8.5 ml glass test tube ◆ 1.5 ml polypropylene cryovial ✓ 5 ml polypropylene cryovial ✓ glass microscope slide ✓ Polyethylene bag
Autoclave ¹	5 cycles at 120°C (248°F) for 20 minutes	<ul style="list-style-type: none"> ✓ 8.5 ml glass test tube ✓ 1.5 ml polypropylene cryovial ✓ 5 ml polypropylene cryovial ✓ 15 ml polypropylene tube ✓ 50 ml polypropylene tube ✓ Glass microscope slide ✓ Vial top
Freezer	5 cycles of 16 hours at -80°C (-112°F) and 8 hours at room temperature	<ul style="list-style-type: none"> ✓ 8.5 ml glass test tube ✓ 1.5 ml polypropylene cryovial ✓ 5 ml polypropylene cryovial ✓ 15 ml polypropylene tube ✓ 50 ml polypropylene tube ✓ Glass microscope slide ✓ Polyethylene bag ✓ Vial top

Liquid Nitrogen	5 cycles of 16 hours at -196°C (-320°F) and 8 hours at room temperature	<ul style="list-style-type: none"> ✓ 8.5 ml glass test tube ✓ 1.5 ml polypropylene cryovial ✓ 5 ml polypropylene cryovial ✓ 15 ml polypropylene tube ✓ 50 ml polypropylene tube ✓ Glass microscope slide ✓ Vial top
Freezer to 50°C (122°F) Water	1 hour at -80°C (-112°F) then placed in 50°C (122°F) water for 10 minutes	<ul style="list-style-type: none"> ✓ 8.5 ml glass test tube ✓ 1.5 ml polypropylene cryovial ✓ 5 ml polypropylene cryovial ✓ 15 ml polypropylene tube ✓ 50 ml polypropylene tube ✓ glass microscope slide ✓ vial top
Liquid Nitrogen to 50°C (122°F) Water	1 hour at -196°C (-320°F) then placed in 50°C (122°F) water for 10 minutes	<ul style="list-style-type: none"> ◆ 8.5 ml glass test tube ◆ 1.5 ml polypropylene cryovial ✓ 5 ml polypropylene cryovial ✓ 15 ml polypropylene tube ✓ 50 ml polypropylene tube ✓ glass microscope slide ✓ vial top

- ✓ = Label suitable for application; no visible effect, label remains adhered to test surface
- ◆ = Label may work in application; test results were mixed
- ¹ = Some color bleed on J40 samples

PERFORMANCE PROPERTY	CHEMICAL RESISTANCE
-----------------------------	----------------------------

The chemical resistance of B-7425J printed with J20 and J40 CMY ink was tested at room temperature. The samples were immersed in the test solvent for 15 minutes. The samples were removed and rubbed 10 times with a cotton swab saturated with the test fluid. The samples were rated for the amount of print removal using the rating scale below.

CHEMICAL REAGENT	SUBJECTIVE OBSERVATION OF VISUAL CHANGE			
	J20 series ink cartridges		J40 series ink cartridges	
	EFFECT TO LABEL STOCK/ADHESIVE	EFFECTS TO PRINTED IMAGE	EFFECT TO LABEL STOCK/ADHESIVE	EFFECTS TO PRINTED IMAGE
Ethanol	No visible effect	1	No visible effect	1
Methanol	No visible effect	1	No visible effect	1
Toluene	Slight adhesive ooze	1	No visible effect	1
Acetone	No visible effect	1	No visible effect	1

Isopropyl Alcohol	No visible effect	1	No visible effect	1
Xylene	Slight adhesive ooze	1	No visible effect	1
10% Formalin	No visible effect	1	Not tested	Not tested
Dimethylsulfoxide (DMSO)	No visible effect	1	No visible effect	2
50% Acetic Acid	No visible effect	1	No visible effect	1
10% Sodium Hydroxide	No visible effect	1	No visible effect	2
10% Chlorox® bleach solution	No visible effect	1	No visible effect	1

Rating Scale:

1 = No visible effect

2 = Effect to printed image

3 = Complete ink / topcoat removal

REGULATORY APPROVALS

For information on the Weee-RoHS compliance status for a Brady Product go to one of the following websites:

In Canada: www.bradycanada.ca/weee-rohs

In Europe: www.bradyeurope.com/rohs

In Japan: www.brady.co.jp/products/labelsuse/rohs

All other regions: www.bradyid.com/weee-rohs

Shelf Life:

Shelf life is two years from the date of receipt for this product as long as this product is stored in its original packaging in an environment below 80° F (27° C) and 60% RH. It remains the responsibility of the user to assess the risk of using this product. We encourage customers to develop testing protocols that will qualify a product's fitness for use in their actual application.

Trademarks:

ANSI: American National Standards Institute (U.S.A.)

ASTM: American Society for Testing and Materials (U.S.A.)

AstroNova® is a registered trademark of AstroNova, Inc.

Clorox® is a registered trademark of The Clorox Company

Epson® is a registered trademark of Seiko Epson Corporation

Polyken™ is a trademark of Testing Machines Inc.

PSTC: Pressure Sensitive Tape Council (U.S.A.)

QuickLabel® is a registered trademark of AstraNova, Inc.

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2021 Brady Worldwide, Inc. | All Rights Reserved

Material may not be reproduced or distributed in any form without written permission.

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 800-292-2289