

Product Compliance













[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 <p>TE Part # 205089-4 HD 20 PIN CONTACT, NON-MAG</p>	 <p>TE Part # 205089-1 HD 20 PIN CONTACT</p>	 <p>TE Part # 205090-1 HD 20 SOCKET CONTACT</p>	 <p>TE Part # 205089-2 PIN CONTACT, SZ 20, AMPLIMITE</p>
 <p>TE Part # 205090-2 SKT CONT ASSY, SZ 20, AMPLIMITE</p>	 <p>TE Part # 1-205089-1 SZ 20 CRIMP PIN CONTACT ASSY</p>	 <p>TE Part # 2334108-2 SOCKET CRIMP CONTACT AWG 20-24</p>	 <p>TE Part # 2334108-3 SOCKET CRIMP CONTACT AWG 22-24</p>
 <p>TE Part # 2334108-4 SOCKET CRIMP CONTACT AWG 24-28</p>	 <p>TE Part # 2334110-2 PIN CRIMP CONTACT AWG 20-24</p>	 <p>TE Part # 2334110-4 PIN CRIMP CONTACT AWG 24-28</p>	 <p>TE Part # 1-205089-0 AMPLIMITE SZ 20 PIN FOR 26-28 AWG</p>
<p>TE Part # 4-205090-1 HD 20 SOCKET CONTACT</p>	<p>TE Part # 1-205089-2 HD 20 PIN CONTACT</p>	<p>TE Part # 1-205089-3 PIN CONTACT, SZ 20, AMPLIMITE, (spooled)</p>	<p>TE Part # 1-205090-0 SKT CONT ASSY, SZ 20, AMPLIMITE (spooled)</p>
<p>TE Part # 205089-6 PIN CONTACT, SZ 20</p>	<p>TE Part # 205090-9 HD 20 SOCKET CONTACT</p>	<p>TE Part # 2-205089-6 CONTACT SIZE 20</p>	


Customers Also Bought



TE Part #1-2199298-4
16P, DIP SKT, 300 CL, LDR, PB FREE




TE Part #9-160313-2
250 PIDG FASTON REC




TE Part #601966-5
K13-1 POSITIONER



TE Part #601966-1
CRIMPING TOOL M22520/2-01




TE Part #9242833001
99M0111-24-0



TE Part #282256-004
81044/12-22-9



TE Part #2176323-3
SMV 2W 150K 5%



TE Part #6-84534-2
1.25MM FFC POST PLATED V 12P



TE Part #169400
CERTI-LOK

Documents

Datasheets & Catalog Pages

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

Bottoming Dies

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[CSA Certificate](#)

English